



1 x TForce 40W 3000K 929002485200

1 x 7200 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.52
 Service downward 0.48

CIE flux code 30 55 79 48 100

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.37	0.35	0.34	0.33	0.32	0.25	0.22	0.18	0.18	0.15	0.09	0.09
0.80	0.46	0.43	0.42	0.41	0.40	0.32	0.27	0.23	0.23	0.19	0.12	0.12
1.00	0.53	0.49	0.49	0.47	0.45	0.38	0.32	0.28	0.27	0.23	0.15	0.15
1.25	0.61	0.56	0.55	0.53	0.51	0.44	0.37	0.33	0.31	0.27	0.18	0.18
1.50	0.66	0.60	0.61	0.58	0.56	0.49	0.41	0.37	0.34	0.30	0.20	0.20
2.00	0.75	0.67	0.68	0.65	0.62	0.56	0.47	0.43	0.39	0.36	0.24	0.24
2.50	0.81	0.72	0.74	0.70	0.66	0.61	0.51	0.48	0.43	0.40	0.27	0.27
3.00	0.86	0.75	0.78	0.73	0.69	0.64	0.55	0.51	0.45	0.43	0.29	0.29
4.00	0.92	0.80	0.84	0.78	0.74	0.69	0.59	0.56	0.49	0.47	0.32	0.32
5.00	0.96	0.83	0.87	0.81	0.76	0.73	0.62	0.59	0.51	0.49	0.34	0.34

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	46150	44496	44070	46590	46567	41297	57021
50.0	50060	47367	43990	43381	45670	39461	53562
55.0	54694	51689	47357	42619	42799	38001	49416
60.0	57046	54421	50818	45059	40099	37123	44274
65.0	56440	53993	51740	47446	39696	34576	37614
70.0	54492	51951	50301	47506	40619	30676	29812
75.0	56152	52979	49467	45606	39835	26749	20552
80.0	64073	59996	54514	47420	37952	22823	12133
85.0	73999	69141	63499	55461	41978	21124	6458
90.0	84459	78685	73269	65067	50686	23921	7112

(cd/m²)

2021-02-04