


1 x Tforce 40W 4000K 929002485300

1 x 7500 lm


Polar intensity diagram



Light output ratio 1.00
 Service upward 0.52
 Service downward 0.48

CIE flux code 30 55 79 48 100

Quantity estimation diagram



Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)												
	0.80 0.80			0.70 0.70 0.70 0.70				0.50 0.50		0.30 0.30			0.00
	0.50 0.50			0.50 0.50 0.50 0.30				0.30 0.10		0.30 0.10			0.00
	0.30 0.10			0.30 0.20 0.10 0.10				0.10 0.10		0.10 0.10			0.00
0.60	0.37	0.35	0.34	0.33	0.32	0.25	0.22	0.18	0.18	0.15	0.09		
0.80	0.46	0.43	0.42	0.41	0.40	0.32	0.27	0.23	0.23	0.19	0.12		
1.00	0.53	0.49	0.49	0.47	0.45	0.38	0.32	0.28	0.27	0.23	0.15		
1.25	0.61	0.56	0.55	0.53	0.51	0.44	0.37	0.33	0.31	0.27	0.18		
1.50	0.66	0.60	0.61	0.58	0.56	0.49	0.41	0.37	0.34	0.30	0.20		
2.00	0.75	0.67	0.68	0.65	0.62	0.56	0.47	0.43	0.39	0.36	0.24		
2.50	0.81	0.72	0.74	0.70	0.66	0.61	0.51	0.48	0.43	0.40	0.27		
3.00	0.86	0.75	0.78	0.73	0.69	0.64	0.55	0.51	0.45	0.43	0.29		
4.00	0.92	0.80	0.84	0.78	0.74	0.69	0.59	0.56	0.49	0.47	0.32		
5.00	0.96	0.83	0.87	0.81	0.76	0.73	0.62	0.59	0.51	0.49	0.34		

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	48073	46350	45906	48532	48507	43017	59397
50.0	52145	49341	45823	45189	47574	41106	55793
55.0	56973	53842	49330	44394	44583	39584	51474
60.0	59423	56688	52935	46936	41770	38670	46119
65.0	58792	56243	53896	49424	41350	36017	39181
70.0	56763	54116	52397	49486	42312	31955	31053
75.0	58492	55187	51529	47506	41496	27864	21407
80.0	66743	62496	56785	49396	39533	23774	12638
85.0	77082	72022	66144	57772	43728	22006	6728
90.0	87979	81963	76322	67778	52798	24916	7405

(cd/m²)

2021-02-04