



1 x 9290035312 33.5W**1 x 6000 lm**


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.48
Service downward 0.52

CIE flux code 18 43 71 52 100

UGRcen (4Hx8H, 0.25H) 29

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.50 0.50	0.30 0.10	0.50 0.50	0.30 0.10	0.50 0.50	0.30 0.10	0.50 0.50	0.30 0.10	0.50 0.50	0.30 0.10	0.50 0.50	0.30 0.10
0.60	0.33	0.31	0.30	0.30	0.29	0.22	0.18	0.14	0.14	0.11	0.06	0.06
0.80	0.42	0.39	0.38	0.37	0.36	0.28	0.24	0.19	0.19	0.15	0.08	0.08
1.00	0.49	0.46	0.45	0.43	0.42	0.34	0.28	0.23	0.23	0.19	0.11	0.11
1.25	0.57	0.52	0.52	0.50	0.48	0.40	0.33	0.28	0.27	0.23	0.14	0.14
1.50	0.62	0.57	0.57	0.54	0.52	0.45	0.37	0.32	0.31	0.27	0.17	0.17
2.00	0.71	0.64	0.65	0.62	0.59	0.52	0.44	0.39	0.36	0.32	0.21	0.21
2.50	0.78	0.69	0.71	0.67	0.63	0.57	0.48	0.44	0.40	0.36	0.24	0.24
3.00	0.83	0.72	0.75	0.71	0.67	0.61	0.52	0.48	0.43	0.40	0.27	0.27
4.00	0.89	0.77	0.81	0.76	0.72	0.66	0.57	0.53	0.47	0.44	0.31	0.31
5.00	0.94	0.80	0.85	0.80	0.75	0.70	0.60	0.57	0.50	0.47	0.33	0.33

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	34984	31067	29024	28387	29024	31067	34984
50.0	36827	32428	30163	29461	30163	32428	36827
55.0	38748	33836	31338	30569	31338	33836	38748
60.0	40764	35300	32556	31716	32556	35300	40764
65.0	42835	36779	33777	32862	33777	36779	42835
70.0	45047	38340	35059	34065	35059	38340	45047
75.0	47400	39974	36390	35310	36390	39974	47400
80.0	50005	41758	37835	36661	37835	41758	50005
85.0	52839	43657	39357	38078	39357	43657	52839
90.0	56107	45811	41073	39674	41073	45811	56107

(cd/m²)

2022-10-26