



1 x 9290020264 A60 2700K 10.5W

1 x 1521 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.34	0.32	0.31	0.31	0.30	0.23	0.19	0.15	0.16	0.12	0.07	0.07
1.00	0.43	0.40	0.39	0.38	0.37	0.29	0.25	0.20	0.20	0.16	0.10	0.10
1.25	0.50	0.47	0.46	0.44	0.43	0.35	0.29	0.25	0.24	0.20	0.12	0.12
1.50	0.57	0.53	0.52	0.50	0.49	0.41	0.34	0.29	0.28	0.24	0.15	0.15
1.75	0.63	0.57	0.58	0.55	0.53	0.45	0.38	0.33	0.32	0.28	0.18	0.18
2.00	0.72	0.64	0.66	0.63	0.60	0.53	0.45	0.40	0.37	0.33	0.22	0.22
2.50	0.79	0.69	0.71	0.68	0.64	0.58	0.49	0.45	0.41	0.37	0.25	0.25
3.00	0.83	0.73	0.76	0.71	0.67	0.62	0.52	0.48	0.44	0.40	0.28	0.28
4.00	0.90	0.78	0.82	0.77	0.72	0.67	0.57	0.54	0.48	0.45	0.31	0.31
5.00	0.94	0.81	0.86	0.80	0.75	0.71	0.60	0.57	0.51	0.48	0.34	0.34

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	9695	8959	8550	8419	8550	8959	9695
50.0	10353	9485	9010	8858	9010	9485	10353
55.0	11126	10100	9547	9372	9547	10100	11126
60.0	12063	10845	10198	9994	10198	10845	12063
65.0	13152	11698	10938	10701	10938	11698	13152
70.0	14440	12691	11793	11515	11793	12691	14440
75.0	15979	13853	12784	12456	12784	13853	15979
80.0	17850	15229	13942	13551	13942	15229	17850
85.0	20190	16893	15321	14849	15321	16893	20190
90.0	23240	18976	17013	16433	17013	18976	23240

(cd/m²)

2019-04-02