



1 x 9290024252 3000K 10.5W

1 x 1521 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.47
Service downward 0.53

CIE flux code 15 40 69 53 100

UGRcen (4Hx8H, 0.25H) 26

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.32	0.31	0.29	0.29	0.28	0.20	0.17	0.12	0.14	0.10	0.05	0.05
1.00	0.41	0.38	0.37	0.36	0.35	0.27	0.23	0.18	0.18	0.14	0.07	0.07
1.25	0.48	0.45	0.44	0.42	0.41	0.33	0.27	0.22	0.22	0.18	0.10	0.10
1.50	0.55	0.51	0.51	0.49	0.47	0.39	0.32	0.27	0.26	0.22	0.13	0.13
2.00	0.61	0.56	0.56	0.53	0.51	0.43	0.36	0.31	0.30	0.25	0.16	0.16
2.50	0.70	0.63	0.64	0.61	0.58	0.51	0.43	0.38	0.35	0.31	0.20	0.20
3.00	0.77	0.68	0.70	0.66	0.63	0.56	0.47	0.43	0.39	0.35	0.23	0.23
4.00	0.82	0.72	0.74	0.70	0.66	0.60	0.51	0.47	0.42	0.39	0.26	0.26
5.00	0.88	0.77	0.80	0.75	0.71	0.66	0.56	0.52	0.47	0.43	0.30	0.30
6.00	0.93	0.80	0.85	0.79	0.74	0.69	0.59	0.56	0.50	0.47	0.33	0.33

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	9943	9187	8768	8634	8768	9187	9943
50.0	10945	10026	9524	9364	9524	10026	10945
55.0	12042	10932	10334	10144	10334	10932	12042
60.0	13255	11917	11205	10982	11205	11917	13255
65.0	14587	12974	12131	11868	12131	12974	14587
70.0	16026	14085	13088	12780	13088	14085	16026
75.0	17689	15336	14152	13789	14152	15336	17689
80.0	19641	16756	15340	14910	15340	16756	19641
85.0	22068	18465	16746	16231	16746	18465	22068
90.0	25254	20620	18487	17857	18487	20620	25254

(cd/m²)

2020-06-16