



1 x 9290023852 2700K 12.2W

1 x 1100 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.33
Service downward 0.67

CIE flux code 28 55 79 67 100

UGRcen (4Hx8H, 0.25H) 25

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.36	0.35	0.34	0.33	0.33	0.25	0.23	0.18	0.20	0.16	0.12	0.12
1.00	0.46	0.43	0.43	0.42	0.40	0.32	0.29	0.24	0.26	0.21	0.16	0.16
1.25	0.53	0.50	0.50	0.48	0.47	0.39	0.35	0.29	0.31	0.26	0.20	0.20
1.50	0.61	0.56	0.57	0.55	0.53	0.45	0.40	0.35	0.36	0.31	0.24	0.24
2.00	0.67	0.61	0.63	0.60	0.57	0.50	0.45	0.39	0.40	0.35	0.28	0.28
2.50	0.76	0.68	0.71	0.68	0.64	0.58	0.52	0.47	0.46	0.42	0.33	0.33
3.00	0.83	0.73	0.77	0.73	0.69	0.63	0.56	0.52	0.50	0.46	0.37	0.37
4.00	0.88	0.77	0.82	0.77	0.73	0.67	0.60	0.56	0.53	0.50	0.40	0.40
5.00	0.94	0.82	0.88	0.82	0.77	0.72	0.65	0.61	0.58	0.55	0.45	0.45
6.00	0.99	0.85	0.92	0.86	0.80	0.76	0.68	0.65	0.61	0.58	0.48	0.48

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	9396	8713	8332	8210	8332	8713	9396
50.0	9513	8747	8325	8191	8325	8747	9513
55.0	9676	8817	8351	8203	8351	8817	9676
60.0	9907	8940	8423	8260	8423	8940	9907
65.0	10197	9103	8528	8348	8528	9103	10197
70.0	10574	9326	8682	8482	8682	9326	10574
75.0	11085	9640	8911	8686	8911	9640	11085
80.0	11740	10042	9205	8950	9205	10042	11740
85.0	12637	10591	9613	9319	9613	10591	12637
90.0	13883	11335	10163	9817	10163	11335	13883

(cd/m²)

2020-06-22