



1 x 9290022850 14W A21 2700K

1 x 1600 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.01
Service upward 0.36
Service downward 0.65

CIE flux code 28 55 79 64 101

UGRcen (4Hx8H, 0.25H) 26

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.37	0.35	0.34	0.34	0.33	0.25	0.23	0.18	0.20	0.16	0.11	0.11
1.00	0.46	0.43	0.43	0.42	0.41	0.33	0.29	0.24	0.25	0.21	0.16	0.16
1.25	0.54	0.50	0.50	0.48	0.47	0.39	0.34	0.29	0.30	0.26	0.19	0.19
1.50	0.61	0.56	0.57	0.55	0.53	0.45	0.40	0.35	0.35	0.31	0.23	0.23
1.75	0.68	0.61	0.63	0.60	0.58	0.50	0.44	0.39	0.39	0.35	0.27	0.27
2.00	0.77	0.69	0.71	0.68	0.65	0.58	0.51	0.47	0.45	0.41	0.32	0.32
2.50	0.83	0.74	0.77	0.73	0.69	0.63	0.56	0.52	0.49	0.46	0.36	0.36
3.00	0.88	0.77	0.82	0.77	0.73	0.67	0.60	0.56	0.53	0.49	0.39	0.39
4.00	0.95	0.82	0.88	0.82	0.77	0.73	0.65	0.61	0.57	0.54	0.43	0.43
5.00	0.99	0.85	0.92	0.86	0.80	0.76	0.68	0.65	0.60	0.57	0.46	0.46

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	17483	15249	14115	13766	14115	15249	17483
50.0	16791	14535	13403	13056	13403	14535	16791
55.0	16165	13892	12764	12420	12764	13892	16165
60.0	15644	13351	12224	11882	12224	13351	15644
65.0	15186	12870	11744	11404	11744	12870	15186
70.0	14820	12473	11344	11004	11344	12473	14820
75.0	14498	12116	10982	10642	10982	12116	14498
80.0	14257	11827	10683	10342	10683	11827	14257
85.0	14060	11575	10417	10074	10417	11575	14060
90.0	14007	11437	10254	9905	10254	11437	14007

(cd/m²)

2019-12-03