



1 x 9290023514 15W BR30 2700K

1 x 1400 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.07
Service downward 0.93

CIE flux code 44 73 91 93 100

UGRcen (4Hx8H, 0.25H) 26

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)												
	0.80 0.80			0.70 0.70 0.70 0.70			0.50 0.50			0.30 0.30			0.00
	0.50 0.50			0.50 0.50 0.50 0.30			0.30 0.10			0.30 0.10			0.00
	0.30 0.10			0.30 0.20 0.10 0.10			0.10 0.10			0.10 0.10			0.00
0.60	0.46	0.44	0.45	0.44	0.43	0.35	0.34	0.30	0.34	0.29	0.27		
0.80	0.56	0.53	0.55	0.53	0.51	0.44	0.43	0.37	0.41	0.37	0.34		
1.00	0.64	0.60	0.63	0.60	0.58	0.51	0.49	0.44	0.48	0.43	0.40		
1.25	0.73	0.67	0.70	0.68	0.65	0.58	0.56	0.51	0.54	0.50	0.47		
1.50	0.79	0.72	0.76	0.73	0.70	0.63	0.61	0.56	0.59	0.55	0.52		
2.00	0.89	0.79	0.86	0.81	0.77	0.71	0.69	0.65	0.67	0.63	0.59		
2.50	0.95	0.84	0.92	0.87	0.82	0.77	0.74	0.71	0.72	0.69	0.65		
3.00	1.00	0.87	0.96	0.91	0.86	0.81	0.78	0.75	0.76	0.73	0.69		
4.00	1.06	0.92	1.02	0.96	0.90	0.86	0.83	0.80	0.80	0.78	0.74		
5.00	1.10	0.94	1.06	0.99	0.93	0.89	0.86	0.84	0.83	0.81	0.77		

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	26307	24093	22883	22497	22883	24093	26307
50.0	23999	21786	20593	20216	20593	21786	23999
55.0	21715	19534	18374	18009	18374	19534	21715
60.0	19480	17354	16240	15893	16240	17354	19480
65.0	17322	15272	14215	13887	14215	15272	17322
70.0	15275	13314	12320	12014	12320	13314	15275
75.0	13374	11510	10583	10300	10583	11510	13374
80.0	11649	9880	9019	8759	9019	9880	11649
85.0	10113	8431	7633	7394	7633	8431	10113
90.0	8802	7187	6443	6224	6443	7187	8802

(cd/m²)

2020-01-20