



1 x 9290023276 16W A21 3000K

1 x 1600 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.34
Service downward 0.66

CIE flux code 27 54 78 66 100

UGRcen (4Hx8H, 0.25H) 28

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.36	0.34	0.34	0.33	0.32	0.25	0.22	0.17	0.19	0.15	0.11	0.11
1.00	0.45	0.42	0.42	0.41	0.40	0.32	0.28	0.23	0.25	0.21	0.15	0.15
1.25	0.53	0.49	0.49	0.48	0.46	0.38	0.34	0.29	0.30	0.25	0.19	0.19
1.50	0.60	0.55	0.56	0.54	0.52	0.44	0.39	0.34	0.35	0.30	0.23	0.23
2.00	0.67	0.60	0.62	0.59	0.57	0.49	0.44	0.39	0.39	0.34	0.27	0.27
2.50	0.76	0.68	0.70	0.67	0.64	0.57	0.51	0.46	0.45	0.41	0.32	0.32
3.00	0.82	0.73	0.76	0.72	0.69	0.62	0.56	0.51	0.49	0.45	0.36	0.36
4.00	0.87	0.76	0.81	0.76	0.72	0.66	0.59	0.55	0.52	0.49	0.39	0.39
5.00	0.94	0.81	0.87	0.81	0.77	0.72	0.64	0.60	0.57	0.54	0.44	0.44
6.00	0.98	0.84	0.91	0.85	0.80	0.75	0.67	0.64	0.60	0.57	0.46	0.46

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	22499	20324	19160	18793	19160	20324	22499
50.0	22369	20028	18792	18405	18792	20028	22369
55.0	22343	19826	18515	18106	18515	19826	22343
60.0	22406	19698	18308	17877	18308	19698	22406
65.0	22561	19643	18166	17712	18166	19643	22561
70.0	22825	19668	18095	17614	18095	19668	22825
75.0	23202	19770	18088	17578	18088	19770	23202
80.0	23730	19970	18162	17618	18162	19970	23730
85.0	24442	20283	18324	17739	18324	20283	24442
90.0	25404	20743	18597	17964	18597	20743	25404

(cd/m²)

2020-03-17