




Candle 25W 2700K E14B35 9290013452

1 x 250 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
Service upward 0.51
Service downward 0.49

CIE flux code 9 34 66 49 100

UGR_{cen} (4Hx8H, 0.25H) 24

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.30	0.10	0.10	0.10	0.10	0.00
0.60	0.31	0.29	0.28	0.27	0.26	0.19	0.15	0.11	0.11	0.08	0.02					
0.80	0.39	0.37	0.35	0.34	0.33	0.25	0.20	0.15	0.16	0.12	0.05					
1.00	0.46	0.43	0.42	0.41	0.39	0.31	0.25	0.20	0.19	0.15	0.07					
1.25	0.54	0.49	0.49	0.47	0.45	0.37	0.30	0.25	0.23	0.19	0.10					
1.50	0.60	0.54	0.54	0.52	0.49	0.41	0.34	0.29	0.27	0.23	0.12					
2.00	0.69	0.61	0.62	0.59	0.56	0.49	0.40	0.35	0.32	0.28	0.16					
2.50	0.75	0.66	0.68	0.64	0.61	0.54	0.45	0.40	0.36	0.32	0.20					
3.00	0.80	0.70	0.72	0.68	0.64	0.58	0.48	0.44	0.39	0.36	0.22					
4.00	0.87	0.75	0.79	0.74	0.69	0.64	0.53	0.50	0.43	0.40	0.26					
5.00	0.92	0.79	0.83	0.77	0.72	0.68	0.57	0.53	0.47	0.44	0.29					

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	5599	5599	5599	5599	5599	5599	5599
50.0	6001	6001	6001	6001	6001	6001	6001
55.0	6353	6353	6353	6353	6353	6353	6353
60.0	6670	6670	6670	6670	6670	6670	6670
65.0	6942	6942	6942	6942	6942	6942	6942
70.0	7195	7195	7195	7195	7195	7195	7195
75.0	7420	7420	7420	7420	7420	7420	7420
80.0	7625	7625	7625	7625	7625	7625	7625
85.0	7811	7811	7811	7811	7811	7811	7811
90.0	7981	7981	7981	7981	7981	7981	7981

(cd/m²)

SL25765-1

2017-03-01