




Candle 25W 2700K E14BA35 9290013458

1 x 250 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
Service upward 0.51
Service downward 0.49

CIE flux code 9 34 66 49 100

UGR_{cen} (4Hx8H, 0.25H) 23

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.30	0.10	0.10	0.10	0.10	0.00
0.60	0.31	0.29	0.28	0.27	0.26	0.19	0.15	0.11	0.11	0.08	0.02					
0.80	0.39	0.37	0.35	0.34	0.33	0.25	0.20	0.15	0.16	0.12	0.05					
1.00	0.46	0.43	0.42	0.41	0.39	0.31	0.25	0.20	0.19	0.15	0.07					
1.25	0.54	0.49	0.49	0.47	0.45	0.37	0.30	0.25	0.23	0.19	0.10					
1.50	0.60	0.54	0.54	0.52	0.49	0.41	0.34	0.29	0.27	0.23	0.12					
2.00	0.69	0.61	0.62	0.59	0.56	0.49	0.40	0.35	0.32	0.28	0.16					
2.50	0.75	0.66	0.68	0.64	0.61	0.54	0.45	0.40	0.36	0.32	0.20					
3.00	0.80	0.70	0.72	0.68	0.64	0.58	0.48	0.44	0.39	0.36	0.22					
4.00	0.87	0.75	0.79	0.74	0.69	0.64	0.53	0.50	0.43	0.40	0.26					
5.00	0.92	0.79	0.83	0.77	0.72	0.68	0.57	0.53	0.47	0.44	0.29					

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	4631	4631	4631	4631	4631	4631	4631
50.0	4933	4933	4933	4933	4933	4933	4933
55.0	5192	5192	5192	5192	5192	5192	5192
60.0	5421	5421	5421	5421	5421	5421	5421
65.0	5613	5613	5613	5613	5613	5613	5613
70.0	5788	5788	5788	5788	5788	5788	5788
75.0	5940	5940	5940	5940	5940	5940	5940
80.0	6074	6074	6074	6074	6074	6074	6074
85.0	6191	6191	6191	6191	6191	6191	6191
90.0	6294	6294	6294	6294	6294	6294	6294

(cd/m²)

SL25765-1

2017-03-02