




Candle 40W 2700K E14B35 9290013453

1 x 470 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
Service upward 0.49
Service downward 0.51

CIE flux code 9 35 66 51 100

UGRcen (4Hx8H, 0.25H) 26

Utilisation factor table

Room Index	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.30	0.10	0.10	0.10	0.10	0.00
0.60	0.30	0.29	0.27	0.27	0.26	0.18	0.15	0.10	0.11	0.07	0.02					
0.80	0.39	0.37	0.35	0.34	0.33	0.25	0.20	0.15	0.16	0.12	0.05					
1.00	0.46	0.43	0.42	0.40	0.39	0.31	0.25	0.20	0.20	0.15	0.07					
1.25	0.54	0.49	0.49	0.47	0.45	0.37	0.30	0.25	0.24	0.19	0.10					
1.50	0.60	0.54	0.54	0.52	0.50	0.41	0.34	0.29	0.27	0.23	0.13					
2.00	0.69	0.61	0.62	0.59	0.56	0.49	0.41	0.35	0.33	0.29	0.17					
2.50	0.75	0.66	0.68	0.64	0.61	0.54	0.45	0.40	0.37	0.33	0.20					
3.00	0.80	0.70	0.72	0.68	0.65	0.58	0.49	0.44	0.40	0.36	0.23					
4.00	0.87	0.75	0.79	0.74	0.69	0.64	0.54	0.50	0.44	0.41	0.27					
5.00	0.92	0.79	0.83	0.77	0.73	0.68	0.57	0.54	0.47	0.44	0.30					

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	11099	11099	11099	11099	11099	11099	11099
50.0	11816	11816	11816	11816	11816	11816	11816
55.0	12466	12466	12466	12466	12466	12466	12466
60.0	13022	13022	13022	13022	13022	13022	13022
65.0	13511	13511	13511	13511	13511	13511	13511
70.0	13935	13935	13935	13935	13935	13935	13935
75.0	14295	14295	14295	14295	14295	14295	14295
80.0	14612	14612	14612	14612	14612	14612	14612
85.0	14875	14875	14875	14875	14875	14875	14875
90.0	15092	15092	15092	15092	15092	15092	15092

(cd/m²)

SL24964-2

2017-03-02