




Bulb 7W 2700K E27A60 9290013873

1 x 806 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
Service upward 0.50
Service downward 0.50

CIE flux code 8 34 66 50 101

UGRcen (4Hx8H, 0.25H) 24

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.50	0.50	0.50	0.50	0.50	0.50	0.30	0.30	0.10	0.10	0.10	0.00	0.00
0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.60	0.30	0.29	0.27	0.27	0.26	0.18	0.15	0.10	0.11	0.07	0.02	0.02
0.80	0.39	0.37	0.35	0.34	0.33	0.25	0.20	0.15	0.16	0.11	0.04	0.04
1.00	0.47	0.43	0.42	0.41	0.39	0.31	0.25	0.20	0.19	0.15	0.07	0.07
1.25	0.54	0.50	0.49	0.47	0.45	0.37	0.30	0.25	0.24	0.19	0.10	0.10
1.50	0.60	0.54	0.54	0.52	0.50	0.42	0.34	0.29	0.27	0.23	0.12	0.12
2.00	0.69	0.62	0.63	0.59	0.57	0.49	0.41	0.35	0.32	0.28	0.17	0.17
2.50	0.76	0.67	0.69	0.65	0.61	0.55	0.45	0.40	0.37	0.33	0.20	0.20
3.00	0.81	0.71	0.73	0.69	0.65	0.59	0.49	0.44	0.40	0.36	0.23	0.23
4.00	0.88	0.76	0.79	0.74	0.70	0.64	0.54	0.50	0.44	0.41	0.27	0.27
5.00	0.92	0.79	0.84	0.78	0.73	0.68	0.58	0.54	0.47	0.44	0.30	0.30

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	5457	5457	5457	5457	5457	5457	5457
50.0	5749	5749	5749	5749	5749	5749	5749
55.0	6217	6217	6217	6217	6217	6217	6217
60.0	6664	6664	6664	6664	6664	6664	6664
65.0	6925	6925	6925	6925	6925	6925	6925
70.0	7209	7209	7209	7209	7209	7209	7209
75.0	7458	7458	7458	7458	7458	7458	7458
80.0	7710	7710	7710	7710	7710	7710	7710
85.0	7961	7961	7961	7961	7961	7961	7961
90.0	8240	8240	8240	8240	8240	8240	8240

(cd/m²)

SL24964-5

2017-03-03