



1 x 9290020258 A60 4000K 8.5W

1 x 1055 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.48
Service downward 0.52

CIE flux code 21 45 72 52 100

UGRcen (4Hx8H, 0.25H) 24

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.34	0.32	0.31	0.31	0.30	0.23	0.19	0.15	0.16	0.12	0.07	0.07
1.00	0.43	0.40	0.39	0.38	0.37	0.29	0.25	0.20	0.20	0.16	0.10	0.10
1.25	0.50	0.47	0.46	0.44	0.43	0.35	0.29	0.25	0.24	0.20	0.12	0.12
1.50	0.57	0.53	0.52	0.50	0.49	0.41	0.34	0.29	0.28	0.24	0.15	0.15
2.00	0.63	0.57	0.58	0.55	0.53	0.45	0.38	0.33	0.32	0.28	0.18	0.18
2.50	0.72	0.64	0.66	0.63	0.60	0.53	0.45	0.40	0.37	0.33	0.22	0.22
3.00	0.79	0.69	0.71	0.68	0.64	0.58	0.49	0.45	0.41	0.37	0.25	0.25
4.00	0.83	0.73	0.76	0.71	0.67	0.62	0.52	0.48	0.44	0.40	0.28	0.28
5.00	0.90	0.78	0.82	0.77	0.72	0.67	0.57	0.54	0.48	0.45	0.31	0.31
5.00	0.94	0.81	0.86	0.80	0.75	0.71	0.60	0.57	0.51	0.48	0.34	0.34

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	6724	6214	5930	5840	5930	6214	6724
50.0	7181	6579	6249	6144	6249	6579	7181
55.0	7717	7006	6622	6501	6622	7006	7717
60.0	8368	7523	7073	6932	7073	7523	8368
65.0	9122	8114	7587	7422	7587	8114	9122
70.0	10016	8803	8180	7987	8180	8803	10016
75.0	11083	9609	8867	8640	8867	9609	11083
80.0	12381	10563	9670	9399	9670	10563	12381
85.0	14003	11717	10626	10299	10626	11717	14003
90.0	16120	13162	11801	11399	11801	13162	16120

(cd/m²)

2019-04-02