



1 x 9290020379 9W 4000K A60

1 x 806 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.22
Service downward 0.78

CIE flux code 34 62 84 78 100

UGRcen (4Hx8H, 0.25H) 28

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.10	0.10	0.00	0.00	0.00	0.00
0.60	0.39	0.38	0.38	0.37	0.36	0.28	0.27	0.22	0.25	0.20	0.17	0.17	0.17	0.17	0.17	0.17
0.80	0.49	0.46	0.47	0.45	0.44	0.36	0.34	0.29	0.31	0.27	0.22	0.22	0.22	0.22	0.22	0.22
1.00	0.57	0.53	0.54	0.52	0.51	0.43	0.40	0.34	0.37	0.32	0.27	0.27	0.27	0.27	0.27	0.27
1.25	0.65	0.59	0.62	0.59	0.57	0.49	0.46	0.40	0.42	0.38	0.32	0.32	0.32	0.32	0.32	0.32
1.50	0.71	0.64	0.67	0.64	0.62	0.54	0.51	0.45	0.47	0.42	0.36	0.36	0.36	0.36	0.36	0.36
2.00	0.81	0.72	0.76	0.72	0.69	0.62	0.58	0.53	0.54	0.50	0.43	0.43	0.43	0.43	0.43	0.43
2.50	0.87	0.77	0.82	0.78	0.74	0.68	0.63	0.59	0.58	0.55	0.48	0.48	0.48	0.48	0.48	0.48
3.00	0.92	0.81	0.87	0.82	0.77	0.72	0.67	0.63	0.62	0.59	0.51	0.51	0.51	0.51	0.51	0.51
4.00	0.98	0.85	0.93	0.87	0.82	0.77	0.72	0.68	0.67	0.64	0.56	0.56	0.56	0.56	0.56	0.56
5.00	1.03	0.88	0.97	0.90	0.85	0.81	0.75	0.72	0.70	0.67	0.59	0.59	0.59	0.59	0.59	0.59

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	29875	27604	26517	26434	27344	29392	32941
50.0	28471	26124	25011	24926	25856	27969	31694
55.0	27181	24762	23628	23542	24489	26661	30559
60.0	25976	23491	22337	22250	23212	25438	29509
65.0	24877	22323	21151	21063	22039	24321	28578
70.0	23806	21186	19998	19909	20897	23232	27681
75.0	22857	20158	18950	18861	19864	22262	26938
80.0	22073	19273	18037	17946	18970	21450	26417
85.0	21409	18481	17211	17118	18169	20752	26085
90.0	20939	17838	16518	16421	17512	20236	26067

(cd/m²)

2019-09-06