




Bulb 100W 2700K E27A70 9290018027

1 x 1521 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
Service upward 0.53
Service downward 0.47

CIE flux code 9 33 65 47 100

UGRcen (4Hx8H, 0.25H) 26

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.10	0.10	0.10	0.10	0.10	0.00
0.60	0.31	0.29	0.28	0.27	0.27	0.19	0.15	0.11	0.11	0.08	0.02					
0.80	0.39	0.37	0.36	0.35	0.34	0.26	0.20	0.16	0.16	0.12	0.04					
1.00	0.47	0.43	0.42	0.41	0.39	0.31	0.25	0.20	0.19	0.15	0.07					
1.25	0.54	0.49	0.48	0.47	0.45	0.37	0.30	0.25	0.23	0.19	0.09					
1.50	0.60	0.54	0.54	0.51	0.49	0.41	0.34	0.28	0.26	0.22	0.11					
2.00	0.69	0.61	0.62	0.59	0.56	0.49	0.40	0.35	0.31	0.27	0.15					
2.50	0.75	0.66	0.68	0.64	0.61	0.54	0.44	0.40	0.35	0.32	0.18					
3.00	0.80	0.70	0.72	0.68	0.64	0.58	0.48	0.43	0.38	0.35	0.21					
4.00	0.87	0.75	0.78	0.73	0.69	0.63	0.53	0.49	0.42	0.39	0.25					
5.00	0.91	0.78	0.82	0.77	0.72	0.67	0.56	0.53	0.45	0.43	0.27					

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	11268	11268	11268	11268	11268	11268	11268
50.0	11995	11995	11995	11995	11995	11995	11995
55.0	12754	12754	12754	12754	12754	12754	12754
60.0	13661	13661	13661	13661	13661	13661	13661
65.0	14588	14588	14588	14588	14588	14588	14588
70.0	15537	15537	15537	15537	15537	15537	15537
75.0	16517	16517	16517	16517	16517	16517	16517
80.0	17406	17406	17406	17406	17406	17406	17406
85.0	18216	18216	18216	18216	18216	18216	18216
90.0	19017	19017	19017	19017	19017	19017	19017

(cd/m²)

SL24964-8

2017-03-03