



1 x 9290022998 6500K 11W E27A60

1 x 1250 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.20
Service downward 0.80

CIE flux code 33 62 84 80 100

UGRcen (4Hx8H, 0.25H) 29

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.39	0.37	0.37	0.36	0.36	0.28	0.26	0.21	0.24	0.20	0.17	0.17
1.00	0.49	0.46	0.47	0.45	0.44	0.36	0.33	0.28	0.31	0.27	0.22	0.22
1.25	0.57	0.53	0.54	0.52	0.51	0.42	0.40	0.34	0.37	0.32	0.28	0.28
1.50	0.65	0.59	0.62	0.59	0.57	0.49	0.46	0.40	0.43	0.38	0.33	0.33
2.00	0.71	0.64	0.67	0.65	0.62	0.54	0.51	0.45	0.47	0.43	0.37	0.37
2.50	0.81	0.72	0.76	0.73	0.69	0.62	0.58	0.53	0.54	0.50	0.44	0.44
3.00	0.87	0.77	0.83	0.78	0.74	0.68	0.63	0.59	0.59	0.55	0.49	0.49
4.00	0.92	0.81	0.87	0.82	0.78	0.72	0.67	0.63	0.63	0.59	0.52	0.52
5.00	0.99	0.85	0.93	0.87	0.82	0.78	0.72	0.69	0.67	0.65	0.57	0.57
5.00	1.03	0.88	0.97	0.91	0.85	0.81	0.76	0.73	0.71	0.68	0.60	0.60

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	40605	36910	34913	34280	34913	36910	40605
50.0	39135	35259	33193	32542	33193	35259	39135
55.0	37528	33505	31389	30728	31389	33505	37528
60.0	36028	31862	29702	29031	29702	31862	36028
65.0	34462	30172	27982	27306	27982	30172	34462
70.0	32952	28538	26322	25642	26322	28538	32952
75.0	31583	27028	24781	24098	24781	27028	31583
80.0	30250	25543	23267	22581	23267	25543	30250
85.0	29165	24250	21927	21233	21927	24250	29165
90.0	28394	23184	20786	20078	20786	23184	28394

(cd/m²)

2019-12-26