



1 x 9290022986 3000K 5W E27A60

1 x 500 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.23
Service downward 0.77

CIE flux code 34 62 84 77 100

UGRcen (4Hx8H, 0.25H) 25

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.39	0.37	0.38	0.37	0.36	0.28	0.26	0.22	0.25	0.20	0.17	0.17
1.00	0.49	0.46	0.47	0.45	0.44	0.36	0.34	0.28	0.31	0.27	0.22	0.22
1.25	0.57	0.53	0.54	0.52	0.51	0.43	0.40	0.34	0.37	0.32	0.27	0.27
1.50	0.65	0.59	0.61	0.59	0.57	0.49	0.46	0.40	0.42	0.38	0.32	0.32
1.75	0.71	0.64	0.67	0.64	0.62	0.54	0.50	0.45	0.46	0.42	0.36	0.36
2.00	0.80	0.72	0.76	0.72	0.69	0.62	0.58	0.53	0.53	0.49	0.43	0.43
2.50	0.87	0.77	0.82	0.78	0.74	0.68	0.63	0.58	0.58	0.54	0.47	0.47
3.00	0.92	0.80	0.87	0.82	0.77	0.72	0.66	0.62	0.61	0.58	0.51	0.51
4.00	0.98	0.85	0.93	0.87	0.82	0.77	0.71	0.68	0.66	0.63	0.55	0.55
5.00	1.03	0.88	0.97	0.90	0.85	0.81	0.75	0.72	0.69	0.67	0.58	0.58

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	15781	14319	13530	13281	13530	14319	15781
50.0	15002	13491	12688	12435	12688	13491	15002
55.0	14267	12714	11900	11646	11900	12714	14267
60.0	13560	11971	11150	10895	11150	11971	13560
65.0	12933	11304	10475	10219	10475	11304	12933
70.0	12406	10728	9887	9630	9887	10728	12406
75.0	11941	10206	9351	9092	9351	10206	11941
80.0	11613	9796	8919	8654	8919	9796	11613
85.0	11401	9474	8564	8292	8564	9474	11401
90.0	11317	9240	8284	8002	8284	9240	11317

(cd/m²)

2019-12-26