



1 x 9290022991 6500K 9W E27A60

1 x 720 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.24
Service downward 0.76

CIE flux code 33 61 83 76 100

UGRcen (4Hx8H, 0.25H) 27

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80			0.70 0.70 0.70 0.70				0.50 0.50			0.30 0.30	
	0.50 0.50	0.30 0.10	0.30 0.10	0.50 0.50	0.30 0.20	0.10 0.10	0.10 0.10	0.30 0.10	0.10 0.10	0.10 0.10	0.10 0.10	0.00
0.60	0.39	0.37	0.37	0.36	0.35	0.28	0.26	0.21	0.24	0.20	0.16	
0.80	0.48	0.45	0.46	0.45	0.43	0.35	0.33	0.28	0.30	0.26	0.21	
1.00	0.56	0.52	0.53	0.52	0.50	0.42	0.39	0.33	0.36	0.31	0.26	
1.25	0.64	0.59	0.61	0.58	0.56	0.48	0.45	0.39	0.41	0.37	0.31	
1.50	0.70	0.64	0.66	0.64	0.61	0.54	0.49	0.44	0.45	0.41	0.35	
2.00	0.80	0.71	0.75	0.72	0.68	0.61	0.57	0.52	0.52	0.48	0.41	
2.50	0.86	0.76	0.81	0.77	0.73	0.67	0.62	0.57	0.57	0.53	0.46	
3.00	0.91	0.80	0.86	0.81	0.76	0.71	0.66	0.61	0.60	0.57	0.49	
4.00	0.98	0.84	0.92	0.86	0.81	0.76	0.71	0.67	0.65	0.62	0.54	
5.00	1.02	0.87	0.96	0.89	0.84	0.80	0.74	0.71	0.68	0.65	0.57	

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	22407	20330	19211	18856	19211	20330	22407
50.0	21502	19336	18185	17823	18185	19336	21502
55.0	20567	18328	17155	16788	17155	18328	20567
60.0	19688	17381	16188	15818	16188	17381	19688
65.0	18819	16449	15242	14870	15242	16449	18819
70.0	18129	15677	14448	14072	14448	15677	18129
75.0	17506	14962	13709	13328	13709	14962	17506
80.0	17050	14382	13094	12706	13094	14382	17050
85.0	16785	13948	12608	12209	12608	13948	16785
90.0	16747	13674	12259	11842	12259	13674	16747

(cd/m²)

2019-12-26