



1 x 9290024416 2700K 7W

1 x 806 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 0.98
Service upward 0.23
Service downward 0.75

CIE flux code 33 60 83 77 98

UGRcen (4Hx8H, 0.25H) 22

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.38	0.36	0.37	0.36	0.35	0.28	0.26	0.21	0.24	0.20	0.16	0.16
1.00	0.48	0.45	0.45	0.44	0.43	0.35	0.32	0.27	0.30	0.25	0.21	0.21
1.25	0.55	0.51	0.52	0.51	0.49	0.41	0.38	0.33	0.35	0.31	0.26	0.26
1.50	0.63	0.58	0.60	0.57	0.55	0.47	0.44	0.39	0.40	0.36	0.30	0.30
1.75	0.69	0.62	0.65	0.62	0.60	0.52	0.48	0.43	0.45	0.40	0.34	0.34
2.00	0.78	0.70	0.74	0.70	0.67	0.60	0.56	0.51	0.51	0.47	0.41	0.41
2.50	0.85	0.75	0.80	0.75	0.72	0.66	0.61	0.56	0.56	0.52	0.45	0.45
3.00	0.89	0.78	0.84	0.79	0.75	0.70	0.64	0.60	0.59	0.56	0.49	0.49
4.00	0.96	0.83	0.90	0.85	0.80	0.75	0.69	0.66	0.64	0.61	0.53	0.53
5.00	1.00	0.86	0.94	0.88	0.83	0.79	0.73	0.70	0.67	0.65	0.57	0.57

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	5045	4620	4388	4314	4388	4620	5045
50.0	4904	4452	4207	4130	4207	4452	4904
55.0	4779	4299	4043	3963	4043	4299	4779
60.0	4665	4156	3889	3805	3889	4156	4665
65.0	4571	4029	3750	3664	3750	4029	4571
70.0	4496	3919	3626	3536	3626	3919	4496
75.0	4441	3821	3513	3419	3513	3821	4441
80.0	4415	3744	3418	3319	3418	3744	4415
85.0	4433	3696	3346	3241	3346	3696	4433
90.0	4500	3674	3294	3182	3294	3674	4500

(cd/m²)

2020-08-14