



1 x 9290030064 6W 3000K

1 x 600 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.38
Service downward 0.62

CIE flux code 28 54 78 62 100

UGRcen (4Hx8H, 0.25H) 27

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.80	0.80	0.70	0.70	0.70
0.60	0.36	0.35	0.34	0.33	0.33	0.25	0.22	0.18	0.19	0.16	0.11	0.36	0.35	0.34	0.33	0.25
0.80	0.46	0.43	0.42	0.41	0.40	0.32	0.28	0.24	0.25	0.21	0.15	0.46	0.43	0.42	0.41	0.32
1.00	0.53	0.49	0.49	0.48	0.46	0.38	0.34	0.29	0.29	0.25	0.18	0.53	0.49	0.49	0.48	0.38
1.25	0.61	0.56	0.56	0.54	0.52	0.44	0.39	0.34	0.34	0.30	0.22	0.61	0.56	0.56	0.54	0.44
1.50	0.67	0.60	0.62	0.59	0.57	0.49	0.43	0.38	0.38	0.34	0.25	0.67	0.60	0.62	0.59	0.49
2.00	0.76	0.68	0.70	0.67	0.63	0.57	0.50	0.45	0.44	0.40	0.30	0.76	0.68	0.70	0.67	0.57
2.50	0.82	0.72	0.76	0.72	0.68	0.62	0.55	0.50	0.48	0.44	0.34	0.82	0.72	0.76	0.72	0.62
3.00	0.87	0.76	0.80	0.76	0.71	0.66	0.58	0.54	0.51	0.48	0.37	0.87	0.76	0.80	0.76	0.66
4.00	0.93	0.81	0.86	0.81	0.76	0.71	0.63	0.59	0.55	0.52	0.41	0.93	0.81	0.86	0.81	0.71
5.00	0.98	0.84	0.90	0.84	0.79	0.75	0.66	0.63	0.58	0.56	0.44	0.98	0.84	0.90	0.84	0.75

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	17213	15707	14840	14492	14618	15234	16423
50.0	17371	15697	14747	14369	14506	15178	16488
55.0	17613	15752	14714	14304	14452	15183	16628
60.0	17984	15907	14768	14322	14482	15281	16878
65.0	18486	16155	14900	14413	14588	15463	17238
70.0	19139	16502	15112	14577	14769	15733	17718
75.0	20050	17026	15467	14875	15087	16161	18409
80.0	21289	17758	15986	15322	15559	16770	19357
85.0	22920	18711	16666	15910	16180	17566	20595
90.0	25204	20030	17615	16737	17049	18670	22311

(cd/m²)

2021-06-25