




1 x 9290024902 8W 2200K-2700K**1 x 806 lm****Polar intensity diagram****Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
 Service upward 0.41
 Service downward 0.59

CIE flux code 25 50 75 59 100

UGRcen (4Hx8H, 0.25H) 24

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80				0.70				0.50				0.30			
	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10
0.60	0.35	0.34	0.33	0.32	0.31	0.24	0.21	0.16	0.18	0.14	0.09	0.09	0.09	0.09	0.09	0.09
0.80	0.44	0.42	0.41	0.40	0.39	0.31	0.27	0.22	0.23	0.19	0.13	0.13	0.13	0.13	0.13	0.13
1.00	0.52	0.48	0.48	0.46	0.45	0.37	0.32	0.27	0.27	0.23	0.16	0.16	0.16	0.16	0.16	0.16
1.25	0.59	0.54	0.55	0.52	0.50	0.43	0.37	0.32	0.32	0.27	0.19	0.19	0.19	0.19	0.19	0.19
1.50	0.65	0.59	0.60	0.57	0.55	0.47	0.41	0.36	0.35	0.31	0.22	0.22	0.22	0.22	0.22	0.22
2.00	0.74	0.66	0.68	0.65	0.62	0.55	0.48	0.43	0.41	0.37	0.27	0.27	0.27	0.27	0.27	0.27
2.50	0.80	0.71	0.74	0.70	0.66	0.60	0.52	0.48	0.45	0.41	0.31	0.31	0.31	0.31	0.31	0.31
3.00	0.85	0.75	0.78	0.74	0.70	0.64	0.56	0.52	0.48	0.45	0.33	0.33	0.33	0.33	0.33	0.33
4.00	0.92	0.79	0.84	0.79	0.74	0.69	0.61	0.57	0.52	0.49	0.37	0.37	0.37	0.37	0.37	0.37
5.00	0.96	0.82	0.88	0.82	0.77	0.73	0.64	0.61	0.55	0.53	0.40	0.40	0.40	0.40	0.40	0.40

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	10212	8922	8266	8063	8266	8922	10212
50.0	10101	8757	8082	7875	8082	8757	10101
55.0	9938	8553	7864	7654	7864	8553	9938
60.0	9882	8444	7737	7522	7737	8444	9882
65.0	9887	8389	7659	7439	7659	8389	9887
70.0	10078	8491	7725	7495	7725	8491	10078
75.0	10390	8689	7879	7636	7879	8689	10390
80.0	10617	8813	7962	7709	7962	8813	10617
85.0	10693	8805	7926	7665	7926	8805	10693
90.0	10293	8404	7535	7278	7535	8404	10293

(cd/m²)

2021-06-23