



1 x 9290030117 2200-2700K 10.5W

1 x 1521 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.01
Service upward 0.44
Service downward 0.57

CIE flux code 19 45 72 56 101

UGRcen (4Hx8H, 0.25H) 26

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.30	0.10	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.60	0.33	0.32	0.31	0.30	0.29	0.22	0.18	0.14	0.15	0.11	0.06	0.06
0.80	0.43	0.40	0.39	0.38	0.37	0.29	0.24	0.19	0.20	0.16	0.10	0.10
1.00	0.50	0.46	0.46	0.44	0.43	0.35	0.29	0.24	0.24	0.20	0.13	0.13
1.25	0.58	0.53	0.53	0.51	0.49	0.41	0.35	0.29	0.29	0.25	0.16	0.16
1.50	0.64	0.58	0.58	0.56	0.53	0.46	0.39	0.34	0.32	0.28	0.19	0.19
2.00	0.73	0.65	0.67	0.63	0.60	0.53	0.45	0.40	0.38	0.34	0.24	0.24
2.50	0.79	0.70	0.72	0.68	0.65	0.58	0.50	0.45	0.42	0.38	0.27	0.27
3.00	0.84	0.74	0.77	0.72	0.68	0.62	0.54	0.49	0.45	0.42	0.30	0.30
4.00	0.91	0.79	0.83	0.78	0.73	0.68	0.59	0.55	0.50	0.47	0.34	0.34
5.00	0.95	0.82	0.87	0.81	0.76	0.72	0.62	0.59	0.53	0.50	0.37	0.37

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	10427	9652	9221	9083	9221	9652	10427
50.0	11194	10274	9770	9609	9770	10274	11194
55.0	11970	10887	10302	10116	10302	10887	11970
60.0	12781	11512	10836	10623	10836	11512	12781
65.0	13714	12220	11438	11193	11438	12220	13714
70.0	14856	13080	12165	11882	12165	13080	14856
75.0	16306	14159	13077	12745	13077	14159	16306
80.0	18088	15452	14155	13761	14155	15452	18088
85.0	20362	17051	15470	14995	15470	17051	20362
90.0	23357	19071	17098	16516	17098	19071	23357

(cd/m²)

2021-07-01