



1 x 9290030105 2200-2700K 5.9W

1 x 806 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.01
Service upward 0.46
Service downward 0.55

CIE flux code 18 43 71 54 101

UGRcen (4Hx8H, 0.25H) 24

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.33	0.32	0.31	0.30	0.29	0.22	0.18	0.14	0.15	0.11	0.06	0.06
1.00	0.42	0.40	0.39	0.38	0.37	0.29	0.24	0.19	0.20	0.15	0.09	0.09
1.25	0.50	0.46	0.45	0.44	0.42	0.34	0.29	0.24	0.24	0.19	0.12	0.12
1.50	0.57	0.52	0.52	0.50	0.48	0.40	0.34	0.29	0.28	0.24	0.15	0.15
1.75	0.63	0.57	0.58	0.55	0.53	0.45	0.38	0.33	0.31	0.27	0.17	0.17
2.00	0.72	0.64	0.66	0.63	0.60	0.52	0.45	0.40	0.37	0.33	0.22	0.22
2.50	0.79	0.69	0.72	0.68	0.64	0.58	0.49	0.45	0.41	0.37	0.25	0.25
3.00	0.83	0.73	0.76	0.72	0.68	0.62	0.53	0.48	0.44	0.41	0.28	0.28
4.00	0.90	0.78	0.82	0.77	0.73	0.67	0.58	0.54	0.48	0.45	0.32	0.32
5.00	0.95	0.81	0.86	0.81	0.76	0.71	0.61	0.58	0.51	0.49	0.35	0.35

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	5586	5159	4923	4847	4923	5159	5586
50.0	5973	5470	5194	5107	5194	5470	5973
55.0	6464	5866	5543	5441	5543	5866	6464
60.0	7047	6332	5953	5834	5953	6332	7047
65.0	7762	6900	6450	6310	6450	6900	7762
70.0	8577	7535	7000	6835	7000	7535	8577
75.0	9472	8208	7573	7378	7573	8208	9472
80.0	10449	8912	8157	7928	8157	8912	10449
85.0	11639	9736	8829	8557	8829	9736	11639
90.0	13153	10740	9629	9301	9629	10740	13153

(cd/m²)

2021-07-01