



1 x 9290030107 2200-2700K 5.9W

1 x 806 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.01
Service upward 0.44
Service downward 0.57

CIE flux code 18 42 71 56 101

UGRcen (4Hx8H, 0.25H) 23

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.33	0.32	0.31	0.30	0.29	0.22	0.18	0.14	0.15	0.11	0.06	0.06
1.00	0.42	0.40	0.39	0.38	0.37	0.28	0.24	0.19	0.20	0.16	0.09	0.09
1.25	0.50	0.46	0.45	0.44	0.42	0.34	0.29	0.24	0.24	0.20	0.12	0.12
1.50	0.57	0.52	0.52	0.50	0.48	0.40	0.34	0.29	0.28	0.24	0.15	0.15
2.00	0.63	0.57	0.58	0.55	0.53	0.45	0.38	0.33	0.32	0.27	0.18	0.18
2.50	0.72	0.64	0.66	0.63	0.60	0.52	0.45	0.40	0.37	0.33	0.23	0.23
3.00	0.79	0.69	0.72	0.68	0.64	0.58	0.49	0.45	0.42	0.38	0.26	0.26
4.00	0.84	0.73	0.76	0.72	0.68	0.62	0.53	0.49	0.45	0.41	0.29	0.29
5.00	0.90	0.78	0.83	0.77	0.73	0.68	0.58	0.54	0.49	0.46	0.33	0.33
5.00	0.95	0.82	0.87	0.81	0.76	0.71	0.62	0.58	0.52	0.50	0.36	0.36

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	3369	3147	3022	2981	3022	3147	3369
50.0	3687	3416	3266	3217	3266	3416	3687
55.0	4088	3755	3572	3513	3572	3755	4088
60.0	4523	4114	3893	3823	3893	4114	4523
65.0	5022	4519	4251	4167	4251	4519	5022
70.0	5564	4946	4622	4522	4622	4946	5564
75.0	6197	5428	5035	4914	5035	5428	6197
80.0	6954	5983	5501	5354	5501	5983	6954
85.0	7958	6695	6087	5905	6087	6695	7958
90.0	9350	7634	6844	6611	6844	7634	9350

(cd/m²)

2021-07-01