



1 x 9290030113 2200-2700K 7.2W

1 x 1055 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.01
Service upward 0.50
Service downward 0.50

CIE flux code 19 43 70 50 101

UGRcen (4Hx8H, 0.25H) 24

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.34	0.32	0.31	0.30	0.30	0.22	0.18	0.14	0.15	0.11	0.06	0.06
1.00	0.43	0.40	0.39	0.38	0.37	0.29	0.24	0.19	0.19	0.15	0.09	0.09
1.25	0.50	0.46	0.46	0.44	0.43	0.35	0.29	0.24	0.23	0.19	0.11	0.11
1.50	0.57	0.53	0.52	0.50	0.48	0.40	0.34	0.29	0.27	0.23	0.14	0.14
1.75	0.63	0.57	0.57	0.55	0.53	0.45	0.38	0.33	0.31	0.27	0.16	0.16
2.00	0.72	0.64	0.65	0.62	0.59	0.52	0.44	0.39	0.36	0.32	0.20	0.20
2.50	0.79	0.69	0.71	0.67	0.64	0.57	0.48	0.44	0.40	0.36	0.23	0.23
3.00	0.83	0.73	0.75	0.71	0.67	0.61	0.52	0.48	0.42	0.39	0.26	0.26
4.00	0.90	0.78	0.81	0.76	0.72	0.67	0.56	0.53	0.47	0.44	0.30	0.30
5.00	0.94	0.81	0.85	0.80	0.75	0.70	0.60	0.56	0.49	0.47	0.32	0.32

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	6275	5799	5534	5450	5534	5799	6275
50.0	6803	6233	5920	5821	5920	6233	6803
55.0	7415	6732	6363	6246	6363	6732	7415
60.0	8147	7324	6887	6749	6887	7324	8147
65.0	9003	8008	7487	7325	7487	8008	9003
70.0	9997	8786	8164	7972	8164	8786	9997
75.0	11170	9684	8937	8707	8937	9684	11170
80.0	12611	10759	9849	9573	9849	10759	12611
85.0	14389	12039	10919	10583	10919	12039	14389
90.0	16687	13625	12216	11800	12216	13625	16687

(cd/m²)

2021-07-01