




Candle 4w 2700K E14B38 9290011398

1 x 250 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
 Service upward 0.57
 Service downward 0.43
 CIE flux code 17 48 78 43 101

UGRcen (4Hx8H, 0.25H) 20

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.10	0.00	0.80	0.80	0.70	0.70
0.60	0.33	0.32	0.30	0.29	0.29	0.21	0.17	0.13	0.13	0.10	0.04		0.33	0.32	0.30	0.29
0.80	0.43	0.40	0.38	0.37	0.36	0.29	0.23	0.19	0.18	0.14	0.07		0.43	0.40	0.38	0.37
1.00	0.50	0.47	0.45	0.44	0.42	0.35	0.28	0.24	0.22	0.18	0.10		0.50	0.47	0.45	0.44
1.25	0.58	0.53	0.52	0.50	0.48	0.41	0.33	0.29	0.26	0.23	0.12		0.58	0.53	0.52	0.50
1.50	0.64	0.58	0.58	0.55	0.53	0.46	0.38	0.33	0.30	0.26	0.15		0.64	0.58	0.58	0.55
2.00	0.73	0.65	0.66	0.63	0.60	0.53	0.44	0.40	0.35	0.32	0.19		0.73	0.65	0.66	0.63
2.50	0.80	0.70	0.72	0.68	0.64	0.59	0.48	0.45	0.39	0.36	0.22		0.80	0.70	0.72	0.68
3.00	0.84	0.74	0.76	0.72	0.68	0.63	0.52	0.48	0.42	0.39	0.24		0.84	0.74	0.76	0.72
4.00	0.91	0.79	0.82	0.77	0.72	0.68	0.56	0.53	0.45	0.43	0.28		0.91	0.79	0.82	0.77
5.00	0.95	0.82	0.86	0.80	0.75	0.71	0.59	0.57	0.48	0.46	0.30		0.95	0.82	0.86	0.80

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	5546	5546	5546	5546	5546	5546	5546
50.0	5967	5967	5967	5967	5967	5967	5967
55.0	5162	5162	5162	5162	5162	5162	5162
60.0	5003	5003	5003	5003	5003	5003	5003
65.0	5322	5322	5322	5322	5322	5322	5322
70.0	4494	4494	4494	4494	4494	4494	4494
75.0	3909	3909	3909	3909	3909	3909	3909
80.0	3556	3556	3556	3556	3556	3556	3556
85.0	3362	3362	3362	3362	3362	3362	3362
90.0	2969	2969	2969	2969	2969	2969	2969

(cd/m²)

sl17255

2015-01-29