




Candle 6w 2700K E14B38 9290011404

1 x 470 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.00
Service upward 0.62
Service downward 0.38

CIE flux code 20 53 79 38 100

UGRcen (4Hx8H, 0.25H) 21

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.80	0.80	0.70	0.70	0.70
0.60	0.34	0.32	0.30	0.29	0.29	0.22	0.17	0.14	0.13	0.10	0.04	0.34	0.32	0.30	0.29	0.22
0.80	0.43	0.40	0.39	0.38	0.37	0.29	0.24	0.19	0.18	0.15	0.07	0.43	0.40	0.39	0.38	0.29
1.00	0.51	0.47	0.46	0.44	0.43	0.35	0.29	0.24	0.22	0.19	0.09	0.51	0.47	0.46	0.44	0.35
1.25	0.58	0.53	0.52	0.50	0.48	0.42	0.34	0.29	0.26	0.23	0.12	0.58	0.53	0.52	0.50	0.42
1.50	0.64	0.58	0.58	0.55	0.53	0.46	0.38	0.33	0.29	0.26	0.14	0.64	0.58	0.58	0.55	0.46
2.00	0.73	0.65	0.66	0.62	0.59	0.53	0.44	0.40	0.34	0.31	0.18	0.73	0.65	0.66	0.62	0.53
2.50	0.79	0.70	0.71	0.67	0.64	0.58	0.48	0.44	0.37	0.35	0.20	0.79	0.70	0.71	0.67	0.58
3.00	0.84	0.73	0.75	0.71	0.67	0.62	0.51	0.47	0.40	0.37	0.22	0.84	0.73	0.75	0.71	0.62
4.00	0.90	0.78	0.81	0.76	0.71	0.67	0.55	0.52	0.43	0.41	0.25	0.90	0.78	0.81	0.76	0.67
5.00	0.94	0.81	0.84	0.79	0.74	0.70	0.58	0.55	0.45	0.44	0.26	0.94	0.81	0.84	0.79	0.70

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	9792	9792	9792	9792	9792	9792	9792
50.0	9720	9720	9720	9720	9720	9720	9720
55.0	8800	8800	8800	8800	8800	8800	8800
60.0	7713	7713	7713	7713	7713	7713	7713
65.0	7900	7900	7900	7900	7900	7900	7900
70.0	6165	6165	6165	6165	6165	6165	6165
75.0	5315	5315	5315	5315	5315	5315	5315
80.0	5733	5733	5733	5733	5733	5733	5733
85.0	5292	5292	5292	5292	5292	5292	5292
90.0	5860	5860	5860	5860	5860	5860	5860

(cd/m²)

SL17112

2015-01-29