



1 x 9290024264 2700K 3.5W

1 x 350 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.30
Service downward 0.70

CIE flux code 23 51 77 70 100

UGRcen (4Hx8H, 0.25H) 24

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.34	0.33	0.32	0.31	0.31	0.23	0.20	0.16	0.18	0.14	0.10	0.10
1.00	0.44	0.41	0.41	0.40	0.39	0.30	0.27	0.22	0.24	0.19	0.14	0.14
1.25	0.51	0.48	0.48	0.46	0.45	0.36	0.33	0.27	0.29	0.24	0.18	0.18
1.50	0.59	0.54	0.55	0.53	0.51	0.43	0.38	0.33	0.34	0.29	0.23	0.23
1.75	0.65	0.59	0.61	0.58	0.56	0.48	0.43	0.37	0.38	0.34	0.26	0.26
2.00	0.75	0.67	0.70	0.66	0.63	0.56	0.50	0.45	0.45	0.40	0.32	0.32
2.50	0.81	0.72	0.76	0.72	0.68	0.61	0.55	0.50	0.49	0.45	0.37	0.37
3.00	0.86	0.76	0.80	0.76	0.72	0.66	0.59	0.55	0.53	0.49	0.40	0.40
4.00	0.93	0.81	0.87	0.81	0.77	0.71	0.64	0.60	0.58	0.55	0.45	0.45
5.00	0.98	0.84	0.91	0.85	0.80	0.75	0.68	0.64	0.61	0.58	0.48	0.48

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	4298	4066	3933	3889	3933	4066	4298
50.0	4602	4322	4163	4112	4163	4322	4602
55.0	4890	4555	4368	4307	4368	4555	4890
60.0	5186	4787	4566	4496	4566	4787	5186
65.0	5496	5020	4761	4679	4761	5020	5496
70.0	5844	5272	4966	4870	4966	5272	5844
75.0	6263	5564	5199	5085	5199	5564	6263
80.0	6808	5931	5486	5349	5486	5931	6808
85.0	7577	6428	5869	5700	5869	6428	7577
90.0	8745	7140	6402	6184	6402	7140	8745

(cd/m²)

2020-07-03