



1 x 9290030130 2200-2700K 3.4W

1 x 470 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.01
Service upward 0.42
Service downward 0.59

CIE flux code 18 43 72 58 101

UGRcen (4Hx8H, 0.25H) 23

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.33	0.32	0.31	0.30	0.29	0.22	0.18	0.14	0.15	0.11	0.06	0.06
1.00	0.42	0.40	0.39	0.38	0.37	0.28	0.24	0.19	0.20	0.16	0.10	0.10
1.25	0.50	0.46	0.46	0.44	0.43	0.34	0.29	0.24	0.24	0.20	0.13	0.13
1.50	0.57	0.52	0.52	0.50	0.48	0.40	0.34	0.29	0.29	0.24	0.16	0.16
1.75	0.63	0.57	0.58	0.55	0.53	0.45	0.39	0.33	0.32	0.28	0.19	0.19
2.00	0.72	0.65	0.66	0.63	0.60	0.53	0.45	0.40	0.38	0.34	0.24	0.24
2.50	0.79	0.70	0.72	0.68	0.65	0.58	0.50	0.45	0.43	0.39	0.28	0.28
3.00	0.84	0.73	0.77	0.72	0.68	0.62	0.54	0.49	0.46	0.42	0.31	0.31
4.00	0.91	0.79	0.83	0.78	0.73	0.68	0.59	0.55	0.50	0.47	0.35	0.35
5.00	0.95	0.82	0.87	0.82	0.77	0.72	0.63	0.59	0.54	0.51	0.38	0.38

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	3257	3099	3007	2977	3007	3099	3257
50.0	3670	3467	3351	3314	3351	3467	3670
55.0	4128	3871	3725	3677	3725	3871	4128
60.0	4610	4285	4103	4045	4103	4285	4610
65.0	5149	4737	4510	4438	4510	4737	5149
70.0	5779	5252	4967	4876	4967	5252	5779
75.0	6584	5891	5526	5411	5526	5891	6584
80.0	7649	6706	6224	6075	6224	6706	7649
85.0	9165	7812	7148	6947	7148	7812	9165
90.0	11583	9458	8479	8190	8479	9458	11583

(cd/m²)

2021-07-01