



Candle 2.0w 2700K E14ST35 9290012385

1 x 250 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.51
Service downward 0.49

CIE flux code 7 33 65 49 101

UGRcen (4Hx8H, 0.25H) 24

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.50	0.50	0.50	0.50	0.50	0.50	0.30	0.30	0.10	0.10	0.10	0.00	0.00
0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.60	0.30	0.29	0.27	0.27	0.26	0.18	0.14	0.10	0.11	0.07	0.01	0.01
0.80	0.39	0.37	0.35	0.34	0.33	0.25	0.20	0.15	0.15	0.11	0.04	0.04
1.00	0.46	0.43	0.42	0.40	0.39	0.31	0.25	0.19	0.19	0.15	0.06	0.06
1.25	0.54	0.49	0.48	0.47	0.45	0.36	0.30	0.24	0.23	0.19	0.09	0.09
1.50	0.60	0.54	0.54	0.52	0.49	0.41	0.34	0.28	0.26	0.22	0.12	0.12
2.00	0.69	0.62	0.62	0.59	0.56	0.49	0.40	0.35	0.32	0.28	0.16	0.16
2.50	0.75	0.67	0.68	0.64	0.61	0.54	0.45	0.40	0.36	0.32	0.19	0.19
3.00	0.80	0.70	0.73	0.68	0.65	0.58	0.48	0.44	0.39	0.35	0.22	0.22
4.00	0.87	0.76	0.79	0.74	0.70	0.64	0.53	0.49	0.43	0.40	0.26	0.26
5.00	0.92	0.79	0.83	0.78	0.73	0.68	0.57	0.53	0.46	0.44	0.29	0.29

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	6031	6031	6031	6031	6031	6031	6031
50.0	6497	6497	6497	6497	6497	6497	6497
55.0	6756	6756	6756	6756	6756	6756	6756
60.0	6973	6973	6973	6973	6973	6973	6973
65.0	7172	7172	7172	7172	7172	7172	7172
70.0	7376	7376	7376	7376	7376	7376	7376
75.0	7566	7566	7566	7566	7566	7566	7566
80.0	7735	7735	7735	7735	7735	7735	7735
85.0	7890	7890	7890	7890	7890	7890	7890
90.0	8024	8024	8024	8024	8024	8024	8024

(cd/m²)

sl 21643-5

2016-03-07