


1 x TLED 15.5W 3000K 9290035772


1 x 1700 lm

Polar intensity diagram

Light output ratio 1.05
 Service upward 0.35
 Service downward 0.70


CIE flux code 32 60 82 67 105

UGRcen (4Hx8H, 0.25H) 24

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.30	0.10	0.30	0.10	0.30	0.10	0.30	0.10	0.30	0.10	0.30	0.10
0.60	0.40	0.38	0.38	0.37	0.36	0.28	0.25	0.21	0.23	0.19	0.14	0.14
0.80	0.50	0.47	0.47	0.45	0.44	0.36	0.32	0.27	0.29	0.25	0.19	0.19
1.00	0.58	0.54	0.54	0.53	0.51	0.43	0.38	0.33	0.34	0.30	0.23	0.23
1.25	0.66	0.61	0.62	0.59	0.57	0.49	0.44	0.39	0.40	0.35	0.28	0.28
1.50	0.72	0.66	0.68	0.65	0.62	0.55	0.49	0.44	0.44	0.40	0.32	0.32
2.00	0.82	0.73	0.77	0.73	0.69	0.63	0.56	0.52	0.50	0.46	0.38	0.38
2.50	0.89	0.78	0.83	0.78	0.74	0.68	0.61	0.57	0.55	0.51	0.42	0.42
3.00	0.94	0.82	0.87	0.82	0.78	0.72	0.65	0.61	0.58	0.55	0.45	0.45
4.00	1.01	0.87	0.94	0.88	0.83	0.78	0.70	0.67	0.63	0.60	0.49	0.49
5.00	1.05	0.90	0.98	0.91	0.86	0.81	0.73	0.70	0.66	0.63	0.52	0.52

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	5617	5648	5881	6093	6554	7482	9002
50.0	5536	5551	5781	5946	6371	7316	8970
55.0	5490	5488	5716	5820	6191	7123	8887
60.0	5476	5457	5686	5719	6019	6898	8727
65.0	5498	5462	5693	5645	5861	6636	8461
70.0	5557	5504	5740	5610	5741	6339	8024
75.0	5643	5579	5831	5626	5679	6050	7459
80.0	5776	5695	5963	5702	5709	5728	6350
85.0	5979	5882	6176	5865	5847	5530	4727
90.0	6245	6137	6477	6172	6243	5925	3423

(cd/m²)

s22060022a

2022-07-11