


1 x TLED 9W 4000K 9290035201


1 x 900 lm

Polar intensity diagram

Light output ratio 0.95
 Service upward 0.30
 Service downward 0.65


CIE flux code 34 61 83 68 95

UGRcen (4Hx8H, 0.25H) 24

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.30	0.10	0.30	0.10	0.30	0.10	0.30	0.10	0.30	0.10	0.30	0.10
0.60	0.37	0.35	0.35	0.34	0.33	0.27	0.24	0.20	0.22	0.18	0.14	0.14
0.80	0.46	0.43	0.43	0.42	0.41	0.34	0.30	0.26	0.27	0.23	0.19	0.19
1.00	0.53	0.49	0.50	0.48	0.47	0.40	0.36	0.31	0.32	0.28	0.23	0.23
1.25	0.61	0.56	0.57	0.55	0.53	0.46	0.41	0.36	0.37	0.33	0.27	0.27
1.50	0.66	0.60	0.62	0.59	0.57	0.50	0.45	0.41	0.41	0.37	0.30	0.30
2.00	0.75	0.67	0.70	0.67	0.64	0.57	0.52	0.48	0.47	0.43	0.35	0.35
2.50	0.81	0.72	0.76	0.72	0.68	0.62	0.56	0.53	0.51	0.48	0.39	0.39
3.00	0.86	0.75	0.80	0.75	0.71	0.66	0.60	0.56	0.54	0.51	0.42	0.42
4.00	0.92	0.79	0.85	0.80	0.75	0.71	0.64	0.61	0.58	0.55	0.46	0.46
5.00	0.96	0.82	0.89	0.83	0.78	0.74	0.67	0.65	0.61	0.58	0.49	0.49

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	5991	5838	5883	5910	6137	6930	8236
50.0	5888	5707	5734	5690	5842	6619	7987
55.0	5831	5615	5619	5494	5557	6288	7680
60.0	5802	5554	5539	5346	5334	5964	7293
65.0	5813	5534	5504	5200	5051	5565	6803
70.0	5864	5553	5508	5113	4847	5171	6148
75.0	5955	5614	5562	5077	4696	4765	5258
80.0	6094	5724	5673	5113	4637	4397	4026
85.0	6289	5890	5847	5239	4710	4201	2407
90.0	6548	6121	6099	5478	4965	4531	1169

(cd/m²)

s22020017a

2022-03-30