


1 x TLED 9W 6500K 9290035202


1 x 900 lm

Polar intensity diagram

Light output ratio 0.97
 Service upward 0.31
 Service downward 0.66


CIE flux code 34 61 83 68 97

UGRcen (4Hx8H, 0.25H) 24

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.38	0.36	0.36	0.35	0.34	0.27	0.25	0.20	0.22	0.18	0.15	0.15
0.80	0.47	0.44	0.44	0.43	0.42	0.34	0.31	0.26	0.28	0.24	0.19	0.19
1.00	0.54	0.50	0.51	0.49	0.48	0.40	0.37	0.32	0.33	0.29	0.23	0.23
1.25	0.62	0.57	0.58	0.56	0.54	0.46	0.42	0.37	0.38	0.34	0.27	0.27
1.50	0.68	0.61	0.63	0.61	0.58	0.51	0.46	0.42	0.42	0.38	0.31	0.31
2.00	0.77	0.68	0.72	0.68	0.65	0.59	0.53	0.49	0.48	0.44	0.36	0.36
2.50	0.83	0.73	0.77	0.73	0.69	0.64	0.58	0.54	0.52	0.49	0.40	0.40
3.00	0.87	0.77	0.82	0.77	0.73	0.68	0.61	0.57	0.55	0.52	0.43	0.43
4.00	0.94	0.81	0.87	0.82	0.77	0.73	0.66	0.63	0.59	0.56	0.47	0.47
5.00	0.98	0.84	0.91	0.85	0.80	0.76	0.69	0.66	0.62	0.60	0.50	0.50

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	6013	5905	5999	6058	6327	7172	8557
50.0	5912	5776	5854	5841	6037	6871	8332
55.0	5846	5681	5743	5649	5759	6547	8040
60.0	5817	5620	5664	5482	5490	6196	7671
65.0	5825	5597	5626	5348	5241	5816	7185
70.0	5868	5614	5635	5259	5030	5410	6527
75.0	5958	5675	5691	5222	4875	4988	5610
80.0	6092	5780	5796	5252	4809	4600	4348
85.0	6230	5901	5937	5353	4870	4385	2738
90.0	6431	6071	6121	5523	5050	4646	1717

(cd/m²)

s22020017b

2022-03-30