



1 x TLED 10W 6500K 240D 9290012775**1 x 1050 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.27
 Service downward 0.73


CIE flux code 36 64 85 73 100

UGRcen (4Hx8H, 0.25H) 24

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80				0.70				0.50			
	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.27	0.22	0.25	0.21	0.17	0.17
0.80	0.50	0.47	0.47	0.46	0.44	0.37	0.34	0.29	0.31	0.27	0.22	0.22
1.00	0.58	0.53	0.54	0.53	0.51	0.43	0.40	0.35	0.36	0.32	0.27	0.27
1.25	0.65	0.60	0.62	0.59	0.57	0.50	0.46	0.41	0.42	0.38	0.31	0.31
1.50	0.72	0.65	0.67	0.65	0.62	0.55	0.50	0.45	0.46	0.42	0.35	0.35
2.00	0.81	0.72	0.76	0.72	0.69	0.63	0.57	0.53	0.52	0.49	0.41	0.41
2.50	0.87	0.77	0.82	0.78	0.74	0.68	0.62	0.58	0.57	0.54	0.46	0.46
3.00	0.92	0.81	0.86	0.81	0.77	0.72	0.66	0.62	0.60	0.57	0.49	0.49
4.00	0.98	0.85	0.92	0.86	0.81	0.77	0.71	0.67	0.65	0.62	0.53	0.53
5.00	1.02	0.88	0.96	0.90	0.84	0.80	0.74	0.71	0.68	0.65	0.56	0.56

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	7214	7154	7106	7145	7394	8128	9836
50.0	6971	6893	6811	6785	6956	7594	9430
55.0	6761	6672	6546	6458	6501	7020	8941
60.0	6588	6483	6336	6177	6094	6427	8404
65.0	6450	6353	6158	5923	5702	5807	7708
70.0	6353	6259	6029	5737	5386	5169	6880
75.0	6328	6227	5974	5649	5146	4526	5837
80.0	6351	6231	6006	5626	4992	3914	4310
85.0	6406	6258	6043	5689	4948	3481	2271
90.0	6506	6360	6131	5775	5078	3447	1020

(cd/m²)

2016-09-12