


T5 26W 3000K 9290019085

1 x

1 x 3600 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.24
Service downward 0.76

CIE flux code 37 65 86 76 100

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.50	0.50	0.50	0.50	0.50	0.50	0.30	0.30	0.10	0.30	0.10	0.00	0.00
0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.60	0.41	0.39	0.39	0.38	0.37	0.30	0.28	0.23	0.26	0.22	0.18	0.18
0.80	0.50	0.47	0.48	0.47	0.45	0.38	0.35	0.30	0.32	0.28	0.24	0.24
1.00	0.58	0.54	0.55	0.54	0.52	0.44	0.41	0.36	0.38	0.34	0.28	0.28
1.25	0.66	0.61	0.63	0.60	0.58	0.51	0.47	0.42	0.43	0.39	0.33	0.33
1.50	0.72	0.66	0.69	0.66	0.63	0.56	0.52	0.47	0.48	0.44	0.37	0.37
2.00	0.82	0.73	0.77	0.73	0.70	0.64	0.59	0.54	0.54	0.51	0.44	0.44
2.50	0.88	0.78	0.83	0.79	0.75	0.69	0.64	0.60	0.59	0.56	0.48	0.48
3.00	0.93	0.81	0.88	0.83	0.78	0.73	0.68	0.64	0.62	0.59	0.52	0.52
4.00	0.99	0.86	0.94	0.88	0.83	0.78	0.72	0.69	0.67	0.64	0.56	0.56
5.00	1.04	0.89	0.97	0.91	0.85	0.82	0.76	0.73	0.70	0.67	0.59	0.59

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	20479	19891	19965	20742	22374	25190	29850
50.0	19902	19149	19079	19728	21264	24081	29065
55.0	19405	18470	18236	18726	20116	22864	28119
60.0	19005	17863	17436	17727	18909	21487	26907
65.0	18692	17320	16674	16728	17637	19926	25355
70.0	18481	16851	15954	15725	16280	18115	23252
75.0	18371	16459	15288	14740	14864	16048	20375
80.0	18391	16184	14730	13846	13483	13809	16330
85.0	18560	16085	14390	13229	12448	11911	10933
90.0	18915	16298	14536	13360	12632	12336	17531

(cd/m²)

2018-03-26