


TLED T8 MasterConnect G2 1 x 929002456800


1 x 2100 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.15
 Service downward 0.85


CIE flux code 38 67 87 85 100

UGRcen (4Hx8H, 0.25H) 30

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.42	0.40	0.39	0.40	0.39	0.39	0.31	0.30	0.25	0.28	0.24	0.21
0.80	0.52	0.49	0.50	0.48	0.47	0.39	0.37	0.32	0.35	0.31	0.27	0.27
1.00	0.60	0.56	0.58	0.56	0.54	0.46	0.44	0.38	0.41	0.37	0.33	0.33
1.25	0.68	0.62	0.65	0.63	0.60	0.53	0.50	0.45	0.47	0.43	0.38	0.38
1.50	0.74	0.67	0.71	0.68	0.65	0.58	0.55	0.50	0.52	0.48	0.43	0.43
2.00	0.84	0.75	0.80	0.76	0.73	0.66	0.63	0.58	0.59	0.55	0.50	0.50
2.50	0.90	0.80	0.86	0.82	0.77	0.72	0.68	0.64	0.64	0.61	0.55	0.55
3.00	0.95	0.83	0.91	0.85	0.81	0.76	0.72	0.68	0.68	0.65	0.59	0.59
4.00	1.02	0.88	0.97	0.91	0.85	0.81	0.77	0.73	0.73	0.70	0.64	0.64
5.00	1.06	0.91	1.01	0.94	0.88	0.84	0.80	0.77	0.76	0.73	0.67	0.67

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	16745	16192	15640	15087	14485	13883	13280
50.0	17528	16825	16122	15419	14613	13806	13000
55.0	18599	17704	16810	15915	14813	13710	12607
60.0	20041	18915	17788	16660	15141	13621	12101
65.0	22157	20710	19264	17819	15698	13578	11457
70.0	25457	23557	21656	19756	16717	13680	10643
75.0	31211	28576	25942	23308	18713	14118	9522
80.0	42737	38749	34760	30770	23111	15452	7792
85.0	77541	69552	61566	53582	37428	21274	5120
90.0	-	-	-	-	-	-	-

(cd/m²)