


1 x TLED 23W 6500K 9290029975

1 x 3700 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.27
Service downward 0.73

CIE flux code 36 64 85 73 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.80	0.80	0.50	0.50	0.70	0.70	0.50	0.50	0.30	0.30	0.10	0.00
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.27	0.22	0.25	0.21	0.17	0.17
0.80	0.50	0.47	0.47	0.46	0.44	0.37	0.34	0.29	0.31	0.27	0.22	0.22
1.00	0.58	0.53	0.54	0.53	0.51	0.43	0.40	0.35	0.36	0.32	0.27	0.27
1.25	0.65	0.60	0.62	0.59	0.57	0.50	0.46	0.41	0.42	0.38	0.31	0.31
1.50	0.72	0.65	0.67	0.65	0.62	0.55	0.50	0.45	0.46	0.42	0.35	0.35
2.00	0.81	0.72	0.76	0.72	0.69	0.63	0.57	0.53	0.52	0.49	0.41	0.41
2.50	0.87	0.77	0.82	0.78	0.74	0.68	0.62	0.58	0.57	0.54	0.46	0.46
3.00	0.92	0.81	0.86	0.81	0.77	0.72	0.66	0.62	0.60	0.57	0.49	0.49
4.00	0.98	0.85	0.92	0.86	0.81	0.77	0.71	0.67	0.65	0.62	0.53	0.53
5.00	1.02	0.88	0.96	0.90	0.84	0.80	0.74	0.71	0.68	0.65	0.56	0.56

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	10169	10123	10089	10184	10590	11697	14248
50.0	9825	9754	9676	9688	9981	10962	13725
55.0	9528	9445	9309	9227	9350	10168	13090
60.0	9287	9183	9016	8839	8779	9348	12395
65.0	9090	8996	8766	8489	8236	8485	11500
70.0	8952	8868	8595	8236	7802	7589	10413
75.0	8919	8826	8526	8121	7473	6696	9029
80.0	8954	8841	8580	8106	7282	5848	6939
85.0	9026	8879	8645	8210	7251	5279	4061
90.0	9173	9030	8781	8362	7488	5330	3540

(cd/m²)

2021-06-10