


1 x TLED 20W 6500K 9290024214

1 x 3000 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.27
Service downward 0.73

CIE flux code 36 64 85 73 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70 0.70 0.70				0.50 0.50 0.30 0.30			
	0.50 0.50	0.30 0.10	0.30 0.10	0.30 0.10	0.50 0.50	0.30 0.10	0.30 0.10	0.30 0.10	0.50 0.50	0.30 0.10	0.30 0.10	0.00
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.27	0.22	0.25	0.21	0.17	0.17
0.80	0.50	0.47	0.47	0.46	0.44	0.37	0.34	0.29	0.31	0.27	0.22	0.22
1.00	0.58	0.53	0.54	0.53	0.51	0.43	0.40	0.35	0.36	0.32	0.27	0.27
1.25	0.65	0.60	0.62	0.59	0.57	0.50	0.46	0.41	0.42	0.38	0.31	0.31
1.50	0.72	0.65	0.67	0.65	0.62	0.55	0.50	0.45	0.46	0.42	0.35	0.35
2.00	0.81	0.72	0.76	0.72	0.69	0.63	0.57	0.53	0.52	0.49	0.41	0.41
2.50	0.87	0.77	0.82	0.78	0.74	0.68	0.62	0.58	0.57	0.54	0.46	0.46
3.00	0.92	0.81	0.86	0.81	0.77	0.72	0.66	0.62	0.60	0.57	0.49	0.49
4.00	0.98	0.85	0.92	0.86	0.81	0.77	0.71	0.67	0.65	0.62	0.53	0.53
5.00	1.02	0.88	0.96	0.90	0.84	0.80	0.74	0.71	0.68	0.65	0.56	0.56

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	14424	14376	14345	14502	15099	16702	20390
50.0	13943	13857	13755	13803	14229	15664	19660
55.0	13518	13415	13238	13148	13350	14543	18778
60.0	13177	13048	12824	12592	12531	13389	17825
65.0	12895	12783	12471	12107	11775	12155	16579
70.0	12706	12601	12234	11751	11157	10896	15098
75.0	12656	12548	12148	11596	10696	9650	13183
80.0	12702	12574	12213	11566	10439	8453	10310
85.0	12802	12622	12313	11724	10413	7657	6207
90.0	13012	12842	12515	11952	10788	7808	8919

(cd/m²)

2020-06-17