


1 x TLED 26W 3000K 9290023523

1 x 3700 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.27
Service downward 0.73

CIE flux code 36 64 85 73 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.40	0.50	0.60	0.38	0.47	0.55	0.27	0.34	0.41	0.25	0.31	0.37
0.80	0.50	0.60	0.70	0.47	0.55	0.63	0.34	0.41	0.49	0.31	0.37	0.44
1.00	0.58	0.68	0.78	0.54	0.63	0.71	0.40	0.47	0.55	0.36	0.42	0.49
1.25	0.65	0.75	0.85	0.62	0.71	0.80	0.46	0.53	0.61	0.42	0.48	0.55
1.50	0.72	0.82	0.92	0.67	0.76	0.85	0.50	0.57	0.65	0.46	0.52	0.59
2.00	0.81	0.91	1.00	0.76	0.85	0.94	0.57	0.65	0.73	0.52	0.58	0.65
2.50	0.87	0.97	1.00	0.82	0.91	1.00	0.62	0.70	0.78	0.57	0.63	0.70
3.00	0.92	1.00	1.00	0.86	0.94	1.00	0.66	0.73	0.81	0.60	0.66	0.73
4.00	0.98	1.00	1.00	0.92	0.98	1.00	0.71	0.77	0.84	0.65	0.71	0.77
5.00	1.02	1.00	1.00	0.96	1.00	1.00	0.74	0.79	0.86	0.68	0.73	0.79

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	17790	17730	17692	17886	18622	20599	25147
50.0	17196	17091	16965	17023	17549	19319	24247
55.0	16672	16545	16327	16216	16465	17937	23160
60.0	16252	16093	15817	15531	15455	16514	21984
65.0	15904	15766	15381	14932	14522	14991	20447
70.0	15671	15541	15089	14493	13760	13438	18621
75.0	15609	15475	14983	14302	13192	11902	16259
80.0	15666	15508	15063	14265	12875	10426	12716
85.0	15789	15567	15187	14460	12843	9443	7655
90.0	16048	15839	15435	14741	13305	9630	11000

(cd/m²)

2020-05-29