


1 x TLED 26W 6500K 9290023525

1 x 3900 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.27
Service downward 0.73

CIE flux code 36 64 85 73 100

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70 0.70 0.70				0.50 0.50 0.30 0.30			
	0.50 0.50	0.30 0.10	0.30 0.20	0.10 0.10	0.50 0.50	0.30 0.10	0.30 0.10	0.10 0.10	0.50 0.50	0.30 0.10	0.30 0.10	0.10 0.10
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.27	0.22	0.25	0.21	0.17	0.17
0.80	0.50	0.47	0.47	0.46	0.44	0.37	0.34	0.29	0.31	0.27	0.22	0.22
1.00	0.58	0.53	0.54	0.53	0.51	0.43	0.40	0.35	0.36	0.32	0.27	0.27
1.25	0.65	0.60	0.62	0.59	0.57	0.50	0.46	0.41	0.42	0.38	0.31	0.31
1.50	0.72	0.65	0.67	0.65	0.62	0.55	0.50	0.45	0.46	0.42	0.35	0.35
2.00	0.81	0.72	0.76	0.72	0.69	0.63	0.57	0.53	0.52	0.49	0.41	0.41
2.50	0.87	0.77	0.82	0.78	0.74	0.68	0.62	0.58	0.57	0.54	0.46	0.46
3.00	0.92	0.81	0.86	0.81	0.77	0.72	0.66	0.62	0.60	0.57	0.49	0.49
4.00	0.98	0.85	0.92	0.86	0.81	0.77	0.71	0.67	0.65	0.62	0.53	0.53
5.00	1.02	0.88	0.96	0.90	0.84	0.80	0.74	0.71	0.68	0.65	0.56	0.56

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	18751	18688	18648	18853	19628	21712	26507
50.0	18126	18015	17882	17943	18497	20363	25558
55.0	17574	17440	17209	17092	17355	18906	24411
60.0	17130	16962	16672	16370	16290	17406	23172
65.0	16764	16618	16212	15739	15307	15801	21552
70.0	16518	16381	15905	15276	14504	14164	19628
75.0	16452	16312	15792	15075	13905	12545	17138
80.0	16512	16346	15877	15036	13571	10989	13403
85.0	16642	16408	16008	15242	13537	9954	8069
90.0	16915	16695	16269	15538	14025	10151	11595

(cd/m²)

2020-05-29