


1 x TLED 16.5W 4000K 9290030445

1 x 2500 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.27
Service downward 0.73

CIE flux code 36 64 85 73 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70 0.70 0.70				0.50 0.50 0.30 0.30			
	0.50 0.50	0.30 0.10	0.30 0.20	0.10 0.10	0.50 0.50	0.30 0.10	0.30 0.10	0.10 0.10	0.50 0.50	0.30 0.10	0.30 0.10	0.10 0.10
0.60	0.40	0.38	0.38	0.37	0.36	0.29	0.27	0.22	0.25	0.21	0.17	0.17
0.80	0.50	0.47	0.47	0.46	0.44	0.37	0.34	0.29	0.31	0.27	0.22	0.22
1.00	0.58	0.53	0.54	0.53	0.51	0.43	0.40	0.35	0.36	0.32	0.27	0.27
1.25	0.65	0.60	0.62	0.59	0.57	0.50	0.46	0.41	0.42	0.38	0.31	0.31
1.50	0.72	0.65	0.67	0.65	0.62	0.55	0.50	0.45	0.46	0.42	0.35	0.35
2.00	0.81	0.72	0.76	0.72	0.69	0.63	0.57	0.53	0.52	0.49	0.41	0.41
2.50	0.87	0.77	0.82	0.78	0.74	0.68	0.62	0.58	0.57	0.54	0.46	0.46
3.00	0.92	0.81	0.86	0.81	0.77	0.72	0.66	0.62	0.60	0.57	0.49	0.49
4.00	0.98	0.85	0.92	0.86	0.81	0.77	0.71	0.67	0.65	0.62	0.53	0.53
5.00	1.02	0.88	0.96	0.90	0.84	0.80	0.74	0.71	0.68	0.65	0.56	0.56

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	15025	14969	14932	15090	15704	17362	21183
50.0	14524	14429	14317	14360	14796	16279	20415
55.0	14081	13968	13778	13678	13880	15109	19487
60.0	13726	13586	13346	13098	13025	13905	18484
65.0	13433	13309	12977	12591	12236	12617	17173
70.0	13235	13119	12730	12219	11591	11304	15616
75.0	13183	13063	12639	12056	11109	10004	13602
80.0	13231	13090	12706	12023	10838	8755	10589
85.0	13335	13139	12809	12184	10805	7919	6295
90.0	13554	13368	13016	12417	11187	8057	7433

(cd/m²)

2021-06-16