


1 x TLED 8W 3000K 9290035572


1 x 1000 lm

Polar intensity diagram

Light output ratio 0.96
 Service upward 0.23
 Service downward 0.73

CIE flux code 36 64 85 76 96


UGRcen (4Hx8H, 0.25H) 24

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80 0.80				0.70 0.70				0.50 0.50				0.30 0.30			
	0.80	0.80	0.50	0.50	0.70	0.70	0.50	0.50	0.30	0.30	0.50	0.50	0.30	0.30	0.10	0.10

0.60	0.39	0.37	0.37	0.36	0.35	0.28	0.26	0.22	0.24	0.20	0.17					
0.80	0.48	0.45	0.46	0.44	0.43	0.36	0.33	0.28	0.31	0.26	0.22					
1.00	0.55	0.51	0.53	0.51	0.49	0.42	0.39	0.34	0.36	0.32	0.27					
1.25	0.63	0.58	0.60	0.57	0.55	0.48	0.45	0.40	0.41	0.37	0.31					
1.50	0.69	0.63	0.65	0.62	0.60	0.53	0.49	0.44	0.45	0.41	0.35					
2.00	0.78	0.70	0.74	0.70	0.67	0.61	0.56	0.52	0.52	0.48	0.41					
2.50	0.84	0.74	0.79	0.75	0.71	0.66	0.61	0.57	0.56	0.53	0.46					
3.00	0.89	0.78	0.84	0.79	0.75	0.70	0.64	0.61	0.59	0.56	0.49					
4.00	0.95	0.82	0.89	0.84	0.79	0.75	0.69	0.66	0.64	0.61	0.53					
5.00	0.99	0.85	0.93	0.87	0.82	0.78	0.72	0.69	0.66	0.64	0.56					

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
------------	-----	------	------	------	------	------	------

45.0	7698	7471	7493	7779	8353	9354	11014
50.0	7453	7179	7163	7419	7938	8912	10639
55.0	7243	6920	6863	7087	7532	8448	10207
60.0	7067	6694	6597	6786	7134	7953	9688
65.0	6917	6500	6368	6529	6752	7424	9049
70.0	6803	6339	6171	6305	6369	6827	8185
75.0	6725	6216	6016	6129	6003	6167	6998
80.0	6682	6128	5898	5998	5673	5487	5389
85.0	6691	6095	5845	5952	5462	4933	3161
90.0	6753	6121	5868	6014	5536	5036	1062

(cd/m²)

/

2022-06-27