


1 x TLED 14W Pink 9290024794


1 x 1000 lm

Polar intensity diagram

Light output ratio 1.04
 Service upward 0.18
 Service downward 0.86


CIE flux code 38 66 87 83 104

UGRcen (4Hx8H, 0.25H) 22

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.43	0.41	0.40	0.42	0.41	0.40	0.31	0.26	0.29	0.25	0.21	0.21
0.80	0.54	0.50	0.52	0.50	0.49	0.40	0.38	0.33	0.36	0.31	0.28	0.28
1.00	0.62	0.57	0.59	0.57	0.56	0.47	0.45	0.39	0.42	0.38	0.33	0.33
1.25	0.70	0.64	0.67	0.65	0.62	0.54	0.51	0.46	0.48	0.44	0.39	0.39
1.50	0.77	0.70	0.73	0.70	0.67	0.60	0.56	0.51	0.53	0.49	0.43	0.43
2.00	0.87	0.77	0.83	0.79	0.75	0.68	0.64	0.59	0.61	0.56	0.51	0.51
2.50	0.94	0.83	0.89	0.84	0.80	0.74	0.70	0.65	0.66	0.62	0.56	0.56
3.00	0.99	0.86	0.94	0.88	0.83	0.78	0.74	0.70	0.69	0.66	0.60	0.60
4.00	1.05	0.91	1.00	0.94	0.88	0.84	0.79	0.75	0.74	0.71	0.65	0.65
5.00	1.10	0.94	1.04	0.97	0.91	0.87	0.82	0.79	0.77	0.75	0.68	0.68

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	4091	3995	4033	4216	4538	5096	6021
50.0	3954	3825	3835	3993	4292	4844	5823
55.0	3793	3643	3635	3778	4042	4570	5582
60.0	3642	3471	3444	3571	3788	4273	5296
65.0	3508	3316	3271	3380	3534	3948	4935
70.0	3386	3175	3113	3209	3287	3599	4489
75.0	3278	3048	2971	3054	3037	3202	3861
80.0	3190	2947	2861	2942	2816	2786	2948
85.0	3132	2875	2782	2866	2644	2409	1538
90.0	3083	2810	2710	2800	2598	2407	125

(cd/m²)

2021-04-28