


1 x TLED 14.5W 3000K 9290035254


1 x 2000 lm

Polar intensity diagram

Light output ratio 1.01
 Service upward 0.24
 Service downward 0.77

CIE flux code 35 63 85 76 101


UGRcen (4Hx8H, 0.25H) 25

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)															
	0.80 0.80				0.70 0.70				0.50 0.50				0.30 0.30			
	0.80	0.80	0.50	0.50	0.70	0.70	0.50	0.50	0.30	0.30	0.50	0.50	0.30	0.30	0.10	0.10

0.60	0.40	0.38	0.38	0.38	0.37	0.29	0.27	0.22	0.25	0.21	0.17					
0.80	0.50	0.47	0.48	0.46	0.45	0.37	0.34	0.29	0.32	0.27	0.23					
1.00	0.58	0.54	0.55	0.53	0.51	0.44	0.40	0.35	0.37	0.33	0.28					
1.25	0.66	0.60	0.62	0.60	0.58	0.50	0.46	0.41	0.43	0.38	0.33					
1.50	0.72	0.65	0.68	0.65	0.63	0.55	0.51	0.46	0.47	0.43	0.37					
2.00	0.82	0.73	0.77	0.73	0.70	0.63	0.59	0.54	0.54	0.50	0.43					
2.50	0.88	0.78	0.83	0.79	0.75	0.69	0.64	0.59	0.59	0.55	0.48					
3.00	0.93	0.82	0.88	0.83	0.78	0.73	0.67	0.63	0.62	0.59	0.51					
4.00	1.00	0.86	0.94	0.88	0.83	0.78	0.72	0.69	0.67	0.64	0.56					
5.00	1.04	0.89	0.98	0.91	0.86	0.82	0.76	0.73	0.70	0.67	0.59					

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	7725	7673	7888	8131	8694	9964	12039
50.0	7490	7414	7619	7803	8318	9592	11814
55.0	7294	7194	7387	7487	7919	9169	11522
60.0	7129	7004	7186	7195	7529	8709	11147
65.0	6993	6844	7019	6931	7158	8171	10538
70.0	6900	6724	6889	6702	6814	7570	9676
75.0	6830	6633	6799	6518	6516	6927	8500
80.0	6795	6576	6746	6384	6288	6231	6630
85.0	6801	6559	6737	6316	6158	5651	3806
90.0	6889	6628	6830	6376	6214	5798	748

(cd/m²)

s22050004a

2022-06-15