


1 x PLC 6.5W4000K120D 9290012015


1 x 700 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.05
 Service downward 0.95


CIE flux code 44 75 92 95 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.46	0.43	0.40	0.45	0.44	0.43	0.35	0.34	0.30	0.34	0.29	0.27
0.80	0.56	0.53	0.50	0.55	0.53	0.52	0.44	0.43	0.38	0.42	0.37	0.35
1.00	0.65	0.60	0.63	0.61	0.59	0.52	0.45	0.50	0.45	0.49	0.44	0.41
1.25	0.73	0.67	0.71	0.69	0.66	0.59	0.57	0.52	0.56	0.51	0.48	0.48
1.50	0.80	0.72	0.77	0.74	0.71	0.64	0.63	0.58	0.61	0.57	0.53	0.53
2.00	0.90	0.80	0.87	0.82	0.79	0.73	0.71	0.66	0.69	0.65	0.62	0.62
2.50	0.96	0.85	0.93	0.88	0.83	0.78	0.76	0.72	0.74	0.70	0.67	0.67
3.00	1.01	0.88	0.97	0.92	0.87	0.82	0.80	0.76	0.77	0.74	0.71	0.71
4.00	1.07	0.93	1.03	0.97	0.91	0.87	0.85	0.82	0.82	0.80	0.76	0.76
5.00	1.11	0.95	1.07	1.00	0.93	0.90	0.88	0.85	0.85	0.83	0.79	0.79

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	25081	20885	18456	17112	16479	16447	16960
50.0	23603	19180	16782	15542	14991	15041	15597
55.0	21945	17393	15077	13976	13533	13691	14219
60.0	19988	15425	13339	12393	12124	12283	12881
65.0	17642	13241	11472	10792	10658	10945	11515
70.0	14855	10901	9589	9181	9226	9562	10083
75.0	11493	8279	7608	7528	7754	8133	8620
80.0	7183	5428	5523	5848	6251	6654	7123
85.0	2370	2743	3644	4334	4885	5361	5818
90.0	50	1202	2549	3454	4145	4651	5102

(cd/m²)

2017-04-06