



1 x 9290018789 7.5W 3000K

1 x 750 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.34
Service downward 0.66

CIE flux code 26 53 78 66 100

UGRcen (4Hx8H, 0.25H) 26

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.36	0.34	0.33	0.33	0.32	0.24	0.22	0.17	0.19	0.15	0.11	0.11
1.00	0.45	0.42	0.42	0.41	0.40	0.32	0.28	0.23	0.25	0.20	0.15	0.15
1.25	0.52	0.49	0.49	0.47	0.46	0.38	0.33	0.28	0.29	0.25	0.19	0.19
1.50	0.60	0.55	0.56	0.54	0.52	0.44	0.39	0.34	0.34	0.30	0.23	0.23
2.00	0.66	0.60	0.62	0.59	0.57	0.49	0.43	0.38	0.38	0.34	0.26	0.26
2.50	0.75	0.67	0.70	0.67	0.64	0.57	0.50	0.45	0.44	0.40	0.32	0.32
3.00	0.82	0.72	0.76	0.72	0.68	0.62	0.55	0.51	0.49	0.45	0.36	0.36
4.00	0.87	0.76	0.81	0.76	0.72	0.66	0.59	0.55	0.52	0.49	0.39	0.39
5.00	0.94	0.81	0.87	0.81	0.77	0.72	0.64	0.60	0.57	0.54	0.43	0.43
6.00	0.98	0.84	0.91	0.85	0.80	0.75	0.67	0.64	0.60	0.57	0.46	0.46

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	21506	18384	16847	16380	16847	18384	21506
50.0	20520	17438	15933	15478	15933	17438	20520
55.0	19637	16596	15123	14679	15123	16596	19637
60.0	18786	15795	14358	13926	14358	15795	18786
65.0	17996	15056	13654	13233	13654	15056	17996
70.0	17226	14342	12976	12568	12976	14342	17226
75.0	16502	13674	12344	11948	12344	13674	16502
80.0	15808	13037	11742	11358	11742	13037	15808
85.0	15197	12472	11208	10834	11208	12472	15197
90.0	14680	11986	10746	10380	10746	11986	14680

(cd/m²)

2018-02-28