



1 x 9290018790 7.5W 4000K

1 x 806 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.34
Service downward 0.66

CIE flux code 26 53 78 66 100

UGRcen (4Hx8H, 0.25H) 27

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80	0.80	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30	0.00	0.00
0.60	0.30	0.10	0.30	0.20	0.10	0.10	0.10	0.10	0.10	0.10	0.00	0.00
0.80	0.36	0.34	0.33	0.33	0.32	0.24	0.22	0.17	0.19	0.15	0.11	0.11
1.00	0.45	0.42	0.42	0.41	0.40	0.32	0.28	0.23	0.25	0.20	0.15	0.15
1.25	0.52	0.49	0.49	0.47	0.46	0.38	0.33	0.28	0.29	0.25	0.19	0.19
1.50	0.60	0.55	0.56	0.54	0.52	0.44	0.39	0.34	0.34	0.30	0.23	0.23
2.00	0.66	0.60	0.62	0.59	0.57	0.49	0.43	0.38	0.38	0.34	0.26	0.26
2.50	0.75	0.67	0.70	0.67	0.64	0.57	0.50	0.45	0.44	0.40	0.32	0.32
3.00	0.82	0.72	0.76	0.72	0.68	0.62	0.55	0.51	0.49	0.45	0.36	0.36
4.00	0.87	0.76	0.81	0.76	0.72	0.66	0.59	0.55	0.52	0.49	0.39	0.39
5.00	0.94	0.81	0.87	0.81	0.77	0.72	0.64	0.60	0.57	0.54	0.43	0.43
6.00	0.98	0.84	0.91	0.85	0.80	0.75	0.67	0.64	0.60	0.57	0.46	0.46

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	23105	19751	18099	17597	18099	19751	23105
50.0	22056	18743	17126	16636	17126	18743	22056
55.0	21102	17834	16252	15775	16252	17834	21102
60.0	20197	16981	15436	14971	15436	16981	20197
65.0	19341	16181	14674	14222	14674	16181	19341
70.0	18516	15417	13949	13510	13949	15417	18516
75.0	17727	14689	13260	12835	13260	14689	17727
80.0	16999	14018	12626	12213	12626	14018	16999
85.0	16316	13389	12033	11631	12033	13389	16316
90.0	15778	12883	11551	11157	11551	12883	15778

(cd/m²)

2018-02-28