

SB Waterproof WT068C G2 provides 3 sizes, standard and through wiring version and 2 CCTs to cater to different customer needs.

SB Waterproof WT068 G2

SB Waterproof WT068C G2 provides flexibility to customer to choose from 3 sizes, standard and through wiring version and 2 CCTs to cater to different customer needs.

Benefits

- Lifetime: 30,000 hrs@L70B50, 3 years warranty
- IP66, IK08
- Through wiring is the option to meet customer needs

Features

- 2 CCTs (NW & CW), 3 lengths (L600, L1200 and L1500), standard and through wiring versions
- High efficacy with 120lm/W
- Reliable with a long lifetime of 30,000 hrs L70
- IP66/IK08: water and dustproof

SB Waterproof WT068 G2


Application

- Parking Garages
- Offices


Versions



SB WATERPROOF



SB WATERPROOF



SB WATERPROOF

SB Waterproof WT068 G2

General Information

Driver included	Yes
Gear	-
Number of gear units	1 unit

Light Technical

Beam angle of light source	- degree(s)
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	80
Luminous Efficacy (rated) (Nom)	120 lm/W
Optic type	Opal

Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220/240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	Yes

Controls and Dimming

Dimmable	No
Maximum dim level	Not applicable

Mechanical and Housing

Optical cover type	Opal
Housing Color	Grey
Mech. impact protection code	IK08
Ingress protection code	IP66

Approval and Application

Ambient temperature range	-20 to +45 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s

Initial Performance (IEC Compliant)

Initial chromaticity	(x=0.31,y=0.33)SD CM≤5
Luminous flux tolerance	-10% / +10%

Light Technical

Order Code	Full Product Name	Luminous Flux
911401862785	WT068C CW LED36 L1200 PSU G2	3,600 lm
911401862685	WT068C CW LED18 L600 PSU G2	1,800 lm
911401862885	WT068C CW LED56 L1500 PSU G2	5,600 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401862785	WT068C CW LED36 L1200 PSU G2	30 W
911401862685	WT068C CW LED18 L600 PSU G2	15 W

Order Code	Full Product Name	Power Consumption
911401862885	WT068C CW LED56 L1500 PSU G2	46.5 W

SB Waterproof WT068 G2

