



Příslušenství pro moduly a předřadníky prezentačního osvětlení v maloobchodním prostředí

Accessories

Předřadníky a příslušenství, které umožňují nabídku celého systému

Vlastnosti

- Kabely
- Upínací prvky
- Profily
- Systém trasování
- Jiné

Aplikace

- Nabídka celého systému s moduly Integrate G4 a předřadníky s konstantním napětím.
- Nabídka celého systému s moduly Integrate S a předřadníky s konstantním napětím.
- Nabídka celého systému s moduly CertaFlux a předřadníky s konstantním napětím.


Versions



Clip Shelf Arm



InteGradeS Mounting Profile 1200




InteGrade engine lock inline




InteGrade spacer cable 0.3m black



InteGrade track cable 0.5mT



InteGrade profile 2000mm



InteGrade mounting clip canopy






InteGrade track 1800mm G






InteGradeS Mounting Profile 900

Versions

	InteGrade power cable 1m black		InteGrade cable 2.5m black
	InteGrade track 1200mm G		InteGrade profile 1175mm
	InteGrade spacer cable 113mm white		InteGrade engin mounting clip G2
	InteGrade connector		InteGrade spacer cable 0.5m white
	InteGrade power cable 2.5m white		InteGrade profile 2000mm Fstyle
	Clip Cannopy 30		InteGrade spacer cable 0.5m white

Versions

	InteGrade mounting clip under shelf		InteGrade cable 2.5m white
	Clip Cannopy 0		InteGrade power cable 2.5m black
			InteGrade engine clip magnetic
	InteGrade power cable 6m white		InteGrade power cable 1m white
	IntegradeS Mounting Clip		InteGrade mounting clip Tstyle profile
			Clip Shelf Front

Versions



InteGrade cable 1m white



InteGrade track power cable 1.5m G




InteGrade magnet Mstyle profile




Clip Shelf Magnetic

Rozměrové výkresy




Product	C1	A1	B1
InteGrade profile 1175mm(46")	11,9 mm	1 175,0 mm	22,2 mm
InteGrade profile 2000mm(79")	11,9 mm	2 000,0 mm	22,2 mm



Product	C1	A1	B1	B2
InteGrade profile 2000mm(79") F style	11,9 mm	2 000,0 mm	31,0 mm	26,0 mm

Rozměrové výkresy

Image
not yet
available




Product				
InteGrade magnet for M style profile				

Product	A1	B1	C1	D1
InteGrade engine lock inline	18,7 mm	10 mm	10,7 mm	4,2 mm


Product	A1	B1	C1	D1
InteGrade mounting clip for T style prof	66,5 mm	19,5 mm	5 mm	4,2 mm

Product	A
InteGrade cable 1m(39") white angle	1 000 mm
InteGrade cable 2.5m(98") black angle	2 500 mm
InteGrade cable 2.5m(98") white angle	2 500 mm


Rozměrové výkresy



Product	A
InteGrade spacer cable 0.5m white	500 mm



Product	A
InteGrade power cable 1m(39") black	1 000 mm
InteGrade power cable 1m(39") white	1 000 mm
InteGrade power cable 2.5m(98") black	2 500 mm
InteGrade power cable 2.5m(98") white	2 500 mm



Product	C1	A1	B1
InteGrade mounting clip under shelf	12,5 mm	47,0 mm	30,5 mm

